


COAXIAL CONNECTOR, SMB, 50 Ohm, Straight PCB jack (female)

82_SMB-50-0-19/111_N

Properties

- Snap-on mechanism provides a fast and reliable connection
- Ideal for applications with high packaging density
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
SMB	jack	IEC 60169-10_MIL-STD-348A/311_CEECC 22130
Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Electrical data		
Impedance		50 Ω
Interface frequency		4 GHz
Mechanical data		
Weight		0.0066 kg
Mating cycles		500
Board mounting type		through holes
Number of printlegs		4
Height above PCB HA		7.45 mm
Height of stand off HS		0 mm
Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min	8 N	8 N
Interface force max	63 N	63 N

COAXIAL CONNECTOR, SMB, 50 Ohm, Straight PCB jack (female)

82_SMB-50-0-19/111_N

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23011018	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23011018	82_SMB-50-0-19/111_NH	Bulk 100 pcs

Additional Information	
Remarks	PCB connector without stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1306 / Date of publication: 12.07.2025 / uncontrolled copy