


COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle PCB jack (female)

85_SMA-50-0-103/111_N

Properties

- Lead free material
- RoHS full compliant without exemption 6C
- Excellent return loss
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
SMA	jack	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0038 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	9.6 mm
Height of stand off HS	0 mm

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle PCB jack (female)

85_SMA-50-0-103/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85201239	RoHS 2011/65/EU and (EU) 2015/863	Compliant without exemption	
	REACH 1907/2006 Article 33 SVHC	Free of SVHC >0,1%	

Ordering Information Table	
Item number	Item description
85201239	85_SMA-50-0-103/111_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31106 / Date of publication: 12.07.2025 / uncontrolled copy