


COAXIAL CONNECTOR, SMC, 50 Ohm, Right angle PCB jack (female)

85_SMC-50-0-1/111_N

Properties

- Screw-on mechanism permits a vibration-proof connection
- Suitable for semi-permanent connections and for use in mobile equipment
- Applicable in frequencies up to 10 GHz



Product configuration

Interface type	Gender	Standard
SMC	jack	IEC 60169-9_MIL-STD-348A/312_CECC 22140

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	10 GHz

Mechanical data

Weight	0.0029 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	8.8 mm
Height of stand off HS	0.5 mm

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SMC, 50 Ohm, Right angle PCB jack (female)

85_SMC-50-0-1/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22640326	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
22652987	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22640326	85_SMC-50-0-1/111_NE	Single
22652987	85_SMC-50-0-1/111_NH	Bulk 100 pcs

Additional Information	
Remarks	PCB connector with stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1262 / Date of publication: 12.07.2025 / uncontrolled copy