

SEN CITY® SC Panel Antenna

91121363

Properties

- 1-Port Panel Antenna
- Frequency Band 380-500
- Vertical Polarization
- Half-power Beam Width 65°
- Gain 12 dBi

**Electrical data**

	Band 1	Band 2
Frequency	380 MHz ... 430 MHz	430 MHz ... 500 MHz
Impedance	50 Ω	50 Ω
VSWR	1.5	1.5
Gain	11.5 dBi	12 dBi
HPBW vertical	37 °	32 °
HPBW horizontal	68 °	63 °
Front to back ratio	18 dB	20 dB
Ambient Temperature	50 °C	50 °C
Composite Power max	500 W	50 W

Electrical remarks

Remarks

IMD level -150 dBc at carrier power 2x 43dBm

Ports

	Port 1
Connector	7/16, jack (female)
Polarization	vertical
DC grounded	Yes

Connections

	Port 1
Band 1	✓
Band 2	✓

SENCITY® SC Panel Antenna

91121363

Mechanical data

Weight	12 kg
Dimensions	992 mm x 492 mm x 190 mm (Height x Width x Depth)
	Windload frontal: 500 N at 150 km/h, lateral: 220 N at 150 km/h , Wind speed survival: 200 km/h
	Packing size (mm): 1140x523x252
	Material: Reflector screen: Weather-proof aluminum. All screws and nuts: Stainless steel
Remarks	Grounding: The metal parts of the antenna including the mounting kit and the inner conductors are DC grounded.
	Ice protection: Due to the very sturdy antenna construction and the protection of the radiating system by the radome, the antenna remains operational even under icy conditions.

Material data

Radome material	Glass Reinforced Plastic (GRP)
Radome colour	Grey
Back plate/base plate material	Aluminium
Back plate/base plate colour	Grey

Environmental data

Environment (application)	Outdoor
---------------------------	---------

Ordering information

Item number	Item description
84467208	91121363

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31259 / Date of publication: 15.01.2025 / uncontrolled copy