

MINI141 CTK-6, SK (male), SK (male), phase invariant, 50 Ohm, 40 GHz, 6 in, 152.4 mm

MINI141 CTK-6

Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 141 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Solderless cable junction
- Low loss PTFE dielectric
- Absolute phase change of <900 ppm over a temperature range of -55°C to +125°C



Product configuration	
Type of cable	MINI141 CT (32322E)
Type description connector A	29094KCR-32322
Type description connector B	29094KCR-32322
Length	152.4 mm
Length	6 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	40 GHz
VSWR max	1.45
Max. insertion loss	1.02 dB
Propagation velocity	80 %

Electrical Data (frequency related)			
Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	23.12 dB	1.15	0.19 dB
2 GHz ... 18 GHz	16.53 dB	1.35	0.59 dB
18 GHz ... 26.5 GHz	15.56 dB	1.4	0.77 dB
26.5 GHz ... 40 GHz	14.71 dB	1.45	1.02 dB

MINI141 CTK-6, SK (male), SK (male), phase invariant, 50 Ohm, 40 GHz, 6 in, 152.4 mm
MINI141 CTK-6

Mechanical data	
Cable diameter	3.61 mm
Static bending radius	8.38 mm
Dynamic bending radius	25.15 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
80355366	MINI141 CTK-6

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P44843 / Date of publication: 04.12.2024 / uncontrolled copy