

## Adapter

**ST adapter, SM / MM, fixed flange with counternut**

FST-FST-C100

**Properties**

- D-shape for panel mount, including fixed nut
- Metal housing, ceramic sleeve

**General data**

Adapter family	ST
Mechanical interface standards	IEC 61754-2, TIA 604-2 (ST)
Number of channels	Simplex
Flange	with flange
Flange type	D-shape Panel Mount, fixed nut integrated and counter nut

**Mechanical data**

Weight	7.5 g
--------	-------

**Environmental data**

Temperature	Operation temperature	-40 °C ... 85 °C
UV resistance	Resistance	Yes

**Optical data**

Mating cycles	200
---------------	-----

**Material data**


Housing material family	Metal
-------------------------	-------

## Adapter

**ST adapter, SM / MM, fixed flange with counternut**

FST-FST-C100

## Technical drawing



## Ordering Information Table

Item number	Item description	Housing color / Adapter key
22650886	FST-FST-C100_100-P	D-shape

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P14514 / Date of publication: 30.06.2025 / uncontrolled copy