


MINIBEND 2SR-14, SMP (female), SMP (female), 50 Ohm, 40 GHz, 14 in, 355.6 mm

MINIBEND 2SR-14

Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29473CR-32-81-1
Series connector A	SMP, straight - jack
Type description connector B	29473CR-32-81-1
Series connector B	SMP, straight - jack
Length	355.6 mm
Length	14 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	40 GHz
VSWR max	1.5
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	19.08 dB	1.25	0.56 dB
2 GHz ... 12.4 GHz	16.54 dB	1.35	1.38 dB
12.4 GHz ... 18 GHz	13.98 dB	1.5	1.78 dB
18 GHz ... 40 GHz	11.73 dB	1.7	

Mechanical data

Cable diameter	2.54 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

MINIBEND 2SR-14, SMP (female), SMP (female), 50 Ohm, 40 GHz, 14 in, 355.6 mm
MINIBEND 2SR-14**Environmental data**

Operation temperature	-55 °C ... 125 °C
-----------------------	-------------------

Ordering information

Item number	Item description
80370951	MINIBEND 2SR-14

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P46161 / Date of publication: 04.12.2024 / uncontrolled copy