

Low-noise coax, 50 Ohm, 1 GHz, 85°C, ø3.15 mm, PVC jacket

G_01130_HT-01

Properties

- Alternative to standard RG cables
- Low noise
- Coax construction



Construction			
Component	Material	Detail	Diameter
Centre conductor	Copper	Wire	0.4 mm
Dielectric	PE (Polyethylene)		1.4 mm
Semi-conductor	PVC (Polyvinyl chloride)		1.9 mm
Outer conductor	Copper		2.4 mm
Jacket	PVC (Polyvinyl chloride)	RAL 7035 - gr	3.15 mm +/- 0.1 mm

Electrical data	
Impedance	50 Ω
Operating frequency	≤ 1 GHz
Capacitance	101 pF/m
Velocity of signal propagation	66 %
Signal delay	5 ns/m
Insulation resistance	100000000 MΩ*m
Operating Voltage (at sea level)	≤ 1.5 kVrms
Test voltage (50 Hz/1 min)	≤ 3 kVrms
Noise level	≤ 10 mV

Mechanical data	
Weight	approx. 16 g/m
Static bending radius	≥ 20 mm
Repeated bending radius	35 mm

Environmental data	
Operation temperature	-25 °C ... 85 °C
Installation temperature	-20 °C ... 60 °C
Fire characteristics	contains halogene

Low-noise coax, 50 Ohm, 1 GHz, 85°C, ø3.15 mm, PVC jacket

G_01130_HT-01

Suitable connectors

Cable group	U3
-------------	----

Ordering information

Item number	Item description	Available as assembly only
22510086	G_01130_HT-01	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1090 / Date of publication: 12.08.2024 / uncontrolled copy