


MULTIFLEX assembly, PC1.85 (male), PC1.85 (male), 50 Ohm, 67 GHz, 152 mm, time delay matched +/- 1 ps

MF86/11PC185/11PC185/152mm

Properties

- Flexible cable assembly
- Applicable up to 67 GHz
- Precise and repeatable measurements
- Absolute phase matched +/- 1ps



Product configuration	
Type of cable	MULTIFLEX_86_HE
Type description connector A	11_PC185-50-2-4/19-_N
Series connector A	PC 1.85, straight - plug
Type description connector B	11_PC185-50-2-4/19-_N
Series connector B	PC 1.85, straight - plug
Length	152 mm
Length type	REF to REF
Electrical data	
Impedance	50 Ω
Max. operating frequency	67 GHz
Signal delay	4.72 ns/m
Propagation velocity	70.6 %
Phase- / Time delay matching	Time delay absolute, +/- 1 ps
Mechanical data	
Weight	15 g
Cable diameter	2.65 mm
Static bending radius	6 mm
Repeated bending radius	20 mm
Environmental data	
Operation temperature	-40 °C ... 70 °C

MULTIFLEX assembly, PC1.85 (male), PC1.85 (male), 50 Ohm, 67 GHz, 152 mm, time delay matched +/- 1 ps

MF86/11PC185/11PC185/152mm

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84150377	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering information	
Item number	Item description
84150377	MF86/11PC185/11PC185/152mm

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35188 / Date of publication: 16.02.2026 / uncontrolled copy