

MICROBEND 2MR-5, SMPM (female), SMPM (female), 50 Ohm, 40 GHz, 5 in, 127 mm

MICROBEND 2MR-5

Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 047 size Semi-Rigid cables
- Tightest bend radius in the MINIBEND family
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



Product configuration

Type of cable	MICROBEND R (32041E)
Type description connector A	29971CR-32-41
Series connector A	SMPM, straight - plug
Type description connector B	29971CR-32-41
Series connector B	SMPM, straight - plug
Length	127 mm
Length	5 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	40 GHz
VSWR max	1.65
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	19.08 dB	1.25	0.39 dB
2 GHz ... 12.4 GHz	16.98 dB	1.33	0.86 dB
12.4 GHz ... 18 GHz	14.72 dB	1.45	1.05 dB
18 GHz ... 40 GHz	12.2 dB	1.65	1.74 dB

Environmental data

Operation temperature	-55 °C ... 125 °C
-----------------------	-------------------

MICROBEND 2MR-5, SMPM (female), SMPM (female), 50 Ohm, 40 GHz, 5 in, 127 mm
MICROBEND 2MR-5

Ordering information	
Item number	Item description
80336500	MICROBEND 2MR-5

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P46517 / Date of publication: 04.12.2024 / uncontrolled copy