


# MICROBEND V-8, 1.85mm (male), 1.85mm (male), 50 Ohm, 65 GHz, 8 in, 203.2 mm

## MICROBEND V-8

### Properties

- Applicable up to 65 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Solderless cable junction
- Direct replacement for 047 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Tightest bend radius in the MINIBEND family



Product configuration	
Type of cable	MICROBEND R (3204IE)
Type description connector A	29890CR-32-4I-1
Series connector A	PC 1.85, straight - plug
Type description connector B	29890CR-32-4I-1
Series connector B	PC 1.85, straight - plug
Length	203.2 mm
Length	8 inch
Length type	REF to REF

Electrical data	
Impedance	50 $\Omega$
Max. operating frequency	65 GHz
VSWR max	1.65
Max. insertion loss	2.65 dB
Propagation velocity	70 %

Electrical Data (frequency related)			
Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 12.4 GHz	18.49 dB	1.27	1.02 dB
12.4 GHz ... 18 GHz	16.53 dB	1.35	1.22 dB
18 GHz ... 40 GHz	13.32 dB	1.55	2.03 dB
40 GHz ... 65 GHz	12.2 dB	1.65	2.65 dB

Mechanical data	
Cable diameter	1.91 mm
Static bending radius	1.52 mm
Dynamic bending radius	4.57 mm

**MICROBEND V-8, 1.85mm (male), 1.85mm (male), 50 Ohm, 65 GHz, 8 in, 203.2 mm**  
MICROBEND V-8

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering information	
Item number	Item description
80366953	MICROBEND V-8

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P45201 / Date of publication: 04.12.2024 / uncontrolled copy