

# MINI141 K-9, 2.9mm (male), 2.9mm (male), 50 Ohm, 40 GHz, 9 in, 228.6 mm

MINI141 K-9

## Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 141 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Solderless cable junction
- Low loss PTFE dielectric



## Product configuration

|                              |                         |
|------------------------------|-------------------------|
| Type of cable                | MINI141 (32022E)        |
| Type description connector A | 29094KCR-32-22          |
| Series connector A           | PC 2.9, straight - plug |
| Type description connector B | 29094KCR-32-22          |
| Series connector B           | PC 2.9, straight - plug |
| Length                       | 228.6 mm                |
| Length                       | 9 inch                  |
| Length type                  | REF to REF              |

## Electrical data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Max. operating frequency | 40 GHz      |
| VSWR max                 | 1.45        |
| Propagation velocity     | 76 %        |

## Electrical Data (frequency related)

| Frequency range     | Return loss | VSWR max | Insertion loss |
|---------------------|-------------|----------|----------------|
| 0 GHz ... 2 GHz     | 23.12 dB    | 1.15     | 0.23 dB        |
| 2 GHz ... 18 GHz    | 16.53 dB    | 1.35     | 0.66 dB        |
| 18 GHz ... 26.5 GHz | 15.56 dB    | 1.4      | 0.81 dB        |
| 26.5 GHz ... 40 GHz | 14.71 dB    | 1.45     | 1.13 dB        |

**MINI141 K-9, 2.9mm (male), 2.9mm (male), 50 Ohm, 40 GHz, 9 in, 228.6 mm**  
MINI141 K-9

| Mechanical data        |                   |
|------------------------|-------------------|
| Cable diameter         | 3.61 mm           |
| Static bending radius  | 8.38 mm           |
| Dynamic bending radius | 25.15 mm          |
| Environmental data     |                   |
| Operation temperature  | -55 °C ... 125 °C |
| Ordering information   |                   |
| Item number            | Item description  |
| 80336735               | MINI141 K-9       |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P38079 / Date of publication: 04.12.2024 / uncontrolled copy