


MINIBEND SR-6, SMA (male), SMP (female), ruggedized, 50 Ohm, 20 GHz, 6 in, 152.4 mm

MINIBEND SR-6

Properties

- Applicable up to 20 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29094CR-32-81
Series connector A	SMA, straight - plug
Type description connector B	29473CR-32-81-1
Series connector B	SMP, straight - jack
Length	152.4 mm
Length	6 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	20 GHz
VSWR max	1.45
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	19.08 dB	1.25	0.31 dB
2 GHz ... 12.4 GHz	17.69 dB	1.3	0.69 dB
12.4 GHz ... 20 GHz	14.71 dB	1.45	1.05 dB

Mechanical data

Cable diameter	2.49 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

MINIBEND SR-6, SMA (male), SMP (female), ruggedized, 50 Ohm, 20 GHz, 6 in, 152.4 mm
MINIBEND SR-6

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering information	
Item number	Item description
80337707	MINIBEND SR-6

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P43796 / Date of publication: 04.12.2024 / uncontrolled copy