


MINIBEND-8HT, SMA (male), SMA (male), lead-free solder, 50 Ohm, 24 GHz, 8 in, 203.2 mm

MINIBEND-8HT

Properties

- Applicable up to 24 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Lead-free solder for RoHS compliance



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29094HTC-32-81
Series connector A	SMA, straight - plug
Type description connector B	29094HTC-32-81
Series connector B	SMA, straight - plug
Length	203.2 mm
Length	8 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	24 GHz
VSWR max	1.4
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	20.82 dB	1.2	0.35 dB
2 GHz ... 12.4 GHz	19.08 dB	1.25	0.82 dB
12.4 GHz ... 18 GHz	16.53 dB	1.35	1.05 dB
18 GHz ... 24 GHz	15.56 dB	1.4	1.22 dB

MINIBEND-8HT, SMA (male), SMA (male), lead-free solder, 50 Ohm, 24 GHz, 8 in, 203.2 mm

MINIBEND-8HT

Mechanical data	
Cable diameter	2.49 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering information	
Item number	Item description
80370240	MINIBEND-8HT

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P38190 / Date of publication: 04.12.2024 / uncontrolled copy