


MINIBEND KR-8HT, 2.9mm (male), 2.9mm (male), lead-free solder, ruggedized, 50 Ohm, 40 GHz, 8 in, 203.2 mm

MINIBEND KR-8HT

Properties

- Applicable up to 40 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Lead-free solder for RoHS compliance



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29094KHTCR-32-81
Series connector A	PC 2.9, straight - plug
Type description connector B	29094KHTCR-32-81
Series connector B	PC 2.9, straight - plug
Length	203.2 mm
Length	8 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	40 GHz
VSWR max	1.5
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	20.83 dB	1.2	0.35 dB
2 GHz ... 26.5 GHz	14.72 dB	1.45	1.29 dB
26.5 GHz ... 40 GHz	13.98 dB	1.5	1.68 dB

MINIBEND KR-8HT, 2.9mm (male), 2.9mm (male), lead-free solder, ruggedized, 50 Ohm, 40 GHz, 8 in, 203.2 mm

MINIBEND KR-8HT

Mechanical data	
Cable diameter	2.54 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering information	
Item number	Item description
80363189	MINIBEND KR-8HT

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P46251 / Date of publication: 04.12.2024 / uncontrolled copy