

MINIBEND L2SR-5, SMP (female), (SMP) female, low-loss, 50 Ohm, 18 GHz, 5 in, 127 mm

MINIBEND L2SR-5

Properties

- Applicable up to 18 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Solderless cable junction
- Low loss PTFE dielectric



Product configuration	
Type of cable	MINIBEND LR (32024E)
Type description connector A	29473CR-32-24-1
Series connector A	SMP, straight - jack
Type description connector B	29473CR-32-24-1
Series connector B	SMP, straight - jack
Length	127 mm
Length	5 inch
Length type	REF to REF

Electrical data	
Impedance	50 Ω
Max. operating frequency	18 GHz
VSWR max	1.5
Propagation velocity	76 %

Electrical Data (frequency related)			
Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	19.08 dB	1.25	0.26 dB
2 GHz ... 12.4 GHz	16.54 dB	1.35	0.58 dB
12.4 GHz ... 18 GHz	13.98 dB	1.5	0.8 dB

Mechanical data	
Cable diameter	2.64 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

MINIBEND L2SR-5, SMP (female), (SMP) female, low-loss, 50 Ohm, 18 GHz, 5 in, 127 mm
MINIBEND L2SR-5

Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
80368563	MINIBEND L2SR-5

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P44135 / Date of publication: 04.12.2024 / uncontrolled copy