

GNSSoF

Power over fiber, 1RU, L1, L2, L5, 16 RF OUT, 1 FO OUT, Monitoring, AC

P-GNSSPoF16-RxE-01

Properties

- Optical power and signal distribution
- Enhanced transmission distance between antenna and receiver
- Power redundancy: two integrated hot swappable power supply modules
- Remote control / monitoring via Web GUI / SNMP / RESTCONF YANG
- Support for remote firmware upgrade
- Support for disabling unused network interfaces

**General data**

Product family	GNSS Power
Suitable Products	O-GNSSPoF0-1-L15, 85227355 O-GNSSPoF0-1-L12, 85244046 Power Supply AC, 85213406
GNSS band	L1 L2 L5
VSWR	< 1.8

Electrical data

GNSS band	L1 L2 L5
VSWR	< 1.8
Equivalent active antenna gain	35 dB
Power consumption	< 36 W
Supply voltage range	100 V AC ... 240 V AC

Mechanical data

Weight	6.7 kg
Dimensions (LxWxH)	482.6mm x 475mm x 43.65mm
Rack height unit	1 U

GNSSoF

Power over fiber, 1RU, L1, L2, L5, 16 RF OUT, 1 FO OUT, Monitoring, AC

P-GNSSPoF16-RxE-01

Environmental data

Storage temperature	-40 °C ... 75 °C
Operation case temperature	-5 °C ... 55 °C

Optical data

Time delay	32 ns
Laser hazard level	4 / 1M
Optical power - signal typical	1 mW
Optical power - remote powering max	600 mW
Operating wavelength signal	1310 nm
Operating wavelength power	1480 nm

Output of RF connection

Product family RF connector	SMA
Gender	Female
Amount of RF connectors	16 pcs

Input of FO connection

Product family FO connector	Q-ODC-12
Gender	Socket
Amount of FO Connectors	1 pcs
Fiber type	Singlemode

Output of FO connection

Product family FO connector	LC UPC
Gender	Plug
Amount of FO Connectors	1 pcs
Fiber type	Singlemode

Network

	RJ 45	SFP	USB
Amount of Connectors	4 pcs	2 pcs	2 pcs
Type 1	1x RS 232	2x Ethernet 10/100/1000 Mbps	1x USB Type A
Type 2	2x Ethernet 10/100/1000 Mbps		1x USB MICRO B
Type 3	1x RS 485		

GNSSoF

Power over fiber, 1RU, L1, L2, L5, 16 RF OUT, 1 FO OUT, Monitoring, AC

P-GNSSPoF16-RxE-01

Technical drawing


Front panel



Back panel



Laser safety

**Diagram**

GNSSoF

Power over fiber, 1RU, L1, L2, L5, 16 RF OUT, 1 FO OUT, Monitoring, AC

P-GNSSPoF16-RxE-01

Ordering Information Table

Item number	Item description
85238861	P-GNSSPoF16-RxE-01

Additional Information

Time delay: in combination with antenna 85227355 O-GNSSPoFO-1-L15

Total link time delay calculation Total delay [ns] = time delay TX [ns]+ time delay RX [ns]+ Time delay single mode fiber 1310nm [ns/m] * link length [m] Example 100m link delay = 32 ns + 32ns + 100m * 4.9 ns/m = 554 ns

Laser safety class:

Safety features are implemented to ensure safe installation and operation which is compliant to a 1M laser class specification. Modification on the system configuration is prohibited.

This RX module is broadband, received frequency bands depend on the connected GNSS antenna.

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P45760 / Date of publication: 25.11.2025 / uncontrolled copy