


MINIBEND R-10, SMA (male), SMA (male), ruggedized, 50 Ohm, 24 GHz, 10 in, 254 mm

MINIBEND R-10

Properties

- Applicable up to 24 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29094CR-32-81
Series connector A	SMA, straight - plug
Type description connector B	29094CR-32-81
Series connector B	SMA, straight - plug
Length	254 mm
Length	10 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	24 GHz
VSWR max	1.4
Max. insertion loss	1.46 dB
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	20.82 dB	1.2	0.41 dB
2 GHz ... 12.4 GHz	19.08 dB	1.25	0.98 dB
12.4 GHz ... 18 GHz	16.53 dB	1.35	1.24 dB
18 GHz ... 24 GHz	15.56 dB	1.4	1.46 dB

MINIBEND R-10, SMA (male), SMA (male), ruggedized, 50 Ohm, 24 GHz, 10 in, 254 mm
MINIBEND R-10**Mechanical data**

Cable diameter	2.54 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm

Environmental data

Operation temperature	-55 °C ... 125 °C
-----------------------	-------------------

Ordering information

Item number	Item description
80337509	MINIBEND R-10

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P38127 / Date of publication: 28.01.2026 / uncontrolled copy