

MINIBEND R-9HT, SMA (male), SMA (male), ruggedized, lead-free solder, 50 Ohm, 24 GHz, 9 in, 228.6 mm

MINIBEND R-9HT

Properties

- Applicable up to 24 GHz
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 086 size Semi-Rigid cables
- Solderless cable junction
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Lead-free solder for RoHS compliance



Product configuration

Type of cable	MINIBEND (32081E)
Type description connector A	29094HTCR-32-81
Series connector A	SMA, straight - plug
Type description connector B	29094HTCR-32-81
Series connector B	SMA, straight - plug
Length	228.6 mm
Length	9 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	24 GHz
VSWR max	1.4
Propagation velocity	70 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	20.82 dB	1.2	0.38 dB
2 GHz ... 12.4 GHz	19.08 dB	1.25	0.91 dB
12.4 GHz ... 18 GHz	16.53 dB	1.35	1.15 dB
18 GHz ... 24 GHz	15.56 dB	1.4	1.35 dB

MINIBEND R-9HT, SMA (male), SMA (male), ruggedized, lead-free solder, 50 Ohm, 24 GHz, 9 in, 228.6 mm
MINIBEND R-9HT

Mechanical data	
Cable diameter	2.54 mm
Static bending radius	5.08 mm
Dynamic bending radius	15.24 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
80365326	MINIBEND R-9HT

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P38182 / Date of publication: 04.12.2024 / uncontrolled copy