

MICROWAVE TEST ASSEMBLIES, 0.8mm (male), 0.8mm (female), 50 Ohm, 145 GHz, 6in

PMAST145/11PC08/21PC08/6in

Properties

- Applicable up to 145 GHz
- Unique phase- and loss stability
- Stock delivery on standard lengths
- Absolute time delay matched +/- 1ps



Product configuration	
Type of cable	Sucotest_145
Type description connector A	SF_11_PC0.8 (straight male)
Type description connector B	SF_21_PC0.8 (straight female)
Length	152 mm
Length	6 inch
Length type	REF to REF
Electrical data	
Impedance	50 Ω
Max. operating frequency	145 GHz
Min. return loss	14 dB
Max. insertion loss	4.97 dB
Propagation velocity	76 %
Amplitude stability vs. flexure	+/- 0.25 dB
Phase stability vs. flexure	+/- 25 °
Phase- / Time delay matching	Time delay absolute, +/- 1 ps
Mechanical data	
Weight	7.2 g
Cable diameter	4.25 mm
Static bending radius	25 mm
Dynamic bending radius	43 mm
Environmental data	
Operation temperature	-40 °C ... 85 °C

MICROWAVE TEST ASSEMBLIES, 0.8mm (male), 0.8mm (female), 50 Ohm, 145 GHz, 6in
PMAST145/11PC08/21PC08/6in

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85271038	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Comment
The test lead up to 145 GHz - for the highest standard of measurement

Ordering information	
Item number	Item description
85271038	PMAST145/11PC08/21PC08/6in

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P60886 / Date of publication: 12.11.2025 / uncontrolled copy