

MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 48in

SF570S/11PC185/11PC185/48in

Properties

- Applicable up to 70 GHz
- High phase- and amplitude stability with flexure and movement
- Excellent insertion and return loss
- Precise and repeatable measurements
- Long life time - lower measurement cost
- Return loss figures are guaranteed up to 67 GHz



Product configuration

Type of cable	SUCOFLEX_570_S
Type description connector A	SF_11_PC185-501
Series connector A	PC 1.85, straight - plug
Type description connector B	SF_11_PC185-501
Series connector B	PC 1.85, straight - plug
Length	1219 mm
Length	48 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	70 GHz
Min. return loss	14 dB
VSWR max	1.499
Max. insertion loss	8.5 dB
Signal delay	4.3 ns/m
Propagation velocity	77 %
Min. screening effectiveness	90 dB
Max. screening frequency	18 GHz
Amplitude stability vs. flexure	+/- 0.05 dB
Phase stability vs. flexure	+/- 8 °

MICROWAVE TEST ASSEMBLIES, 1.85mm (male), 1.85mm (male), 50 Ohm, 70 GHz, 48in SF570S/11PC185/11PC185/48in

Mechanical data			
Cable diameter		5.8 mm	
Static bending radius		25.4 mm	
Environmental data			
Operation temperature		-55 °C ... 125 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85186160	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
Comment			
SUCOFLEX 570S microwave cable assemblies set a new measurement standard through 70 GHz			
Return loss figures are guaranteed up to 67 GHz.			
Ordering information			
Item number	Item description		
85186160	SF570S/11PC185/11PC185/48in		

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P37461 / Date of publication: 10.04.2025 / uncontrolled copy