

MICROWAVE TEST ASSEMBLIES, SMA (male), SMA (male), 50 Ohm, 8 GHz, 600mm

TL-8A-11SMA-11SMA-00600-51

Properties

- Applicable up to 8 GHz
- High flexibility in spite of armouring



Product configuration	
Type of cable	TL-8A
Type description connector A	11_SMA-50-4-74/199_N
Series connector A	SMA, straight - plug
Type description connector B	11_SMA-50-4-74/199_N
Series connector B	SMA, straight - plug
Armour	A-Armour blue SF 103/104/126/TL-8A, 85°C, Ø10.2mm,PUR jacket
Length	600 mm
Length type	REF to REF
Electrical data	
Impedance	50 Ω
Max. operating frequency	8 GHz
Min. return loss	22 dB
VSWR max	1.173
Max. insertion loss	0.88 dB
Signal delay	4.12 ns/m
Propagation velocity	81 %
CW Power at 40°	50 W at 8 GHz
Mechanical data	
Weight	0.17 kg
Cable diameter	10.3 mm
Static bending radius	55 mm
Environmental data	
Operation temperature	-40 °C ... 85 °C

MICROWAVE TEST ASSEMBLIES, SMA (male), SMA (male), 50 Ohm, 8 GHz, 600mm
TL-8A-11SMA-11SMA-00600-51

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85014636	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Comment
Test assembly for indoor applications (Test and Measurement) consisting of a high flexible PE foamed cable with armouring protection and 2x SMA male straight connectors for frequency up to 8.0 GHz.

Ordering information	
Item number	Item description
85014636	TL-8A-11SMA-11SMA-00600-51

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P647 / Date of publication: 10.04.2025 / uncontrolled copy