

RFPC-MMCX05-F : MMCX Right Angle Jack, Surface Mount Type

Material and Plating:

Insulator: Teflon

Pin: Beryllium Copper, Gold

Body: Brass, Gold

Specification:

Durability: 500 Mating Cycles Min.




Operating Temperature: -40°C~+125°C

Working Frequency Range: DC~6GHz


Impedance: 50 ohm.

Notes:

1. The tape & reel packaging is available but not tooled,
contact GradConn for more detail.



Recommended PCB SMT Layout



HOW TO ORDER

R F P C - M M C X 0 5 - F - X

PACKAGING OPTIONS:

T = TRAY

R = TAPE & REEL (SEE NOTES 1.)

REV. DATE & DRN
11 24/02/20 - NYW RELEASE
12 24/02/20 - NYW ADD MATING HEIGHT DIAGRAM
13 24/02/20 - NYW ADD WORKING TEMP.
14 24/02/20 - NYW ADD IMPEDANCE
15 24/02/20 - NYW ADD GET LOGO

Scale: NTS	THIRD ANGLE	Unstated Tolerances:	Material
Drawn: NYW		.X ±0.2	SEE NOTE
App'd: XXX	Title JACK	.XX ±0.2	NOT TO SCALE
Date: 9 MAY '25	Revision: 1.4	.XXX ±0.2	Unit: mm
		ANGLES ±5	

THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE
COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT

Type: RFPC-MMCX05-F

RFPC-MMCX05-F

Drawing Number:

Sheet 1 of 1

Drawing © E and O E