

RAFIX 16, buzzer, round collar, 70 dB**Description**

Acoustic signal generator, available in three collar shapes to match the design of the RAFIX 16 actuators.

**technical data****> general**

Bezel color	black	direct links
Property of bezel / mushroom	opaque	> RAFI eCatalog
Collar shape	round	
Frequency	2,400 - 3100 Hz	
Operating temperature, min.	-25 °C	
Operating temperature, max.	70 °C	
Storage temperature, min.	-40 °C	
Storage temperature, max.	85 °C	
Volume 1 m	70 dB	
illuminated	No	
Tone type	Continuous tone	
Packaging	Box	
Packaging unit	2 pcs.	
Net weight	8.5 g	
Degree of protection, front side, according to DIN EN 60529	IP65	
Environment resistance	IEC 60068-2-14 IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78	
Minimum order quantity (MOQ)	10 pcs.	
RoHS compliant	Yes	
REACH compliant	Yes	
Country of origin	HU	

> mounting diameters

Outside dimension, length	24.95 mm
Outside dimension, width	24.95 mm
Outside dimension, height	37.45 mm
Mounting hole	16.2 mm
Mounting depth	30.5 mm
Installation height	6.95 mm
Grid, min.	25 x 25 mm
Collar dimension	ø 24.95 mm

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Feb 8, 2026 **page:** 1/3

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
88276 Berg / Ravensburg
Germany
www.rafi-group.com,
info.headquarters@rafi-group.com

> mechanical data

Terminal on the rear	Flat quick-connect terminal 2.8 x 0.8
Fixing	Threaded ring
Threaded ring torque, max.	1.2 Nm


> electrical data

Voltage type	DC
Rated operating voltage	24 V
Power loss	0.60000 W

Use according to UL:

RAFIX control devices are defined at RAFI as modular elements, consisting of an actuating element, if necessary a coupling and an individual contact or lighting unit.

Actuating elements (such as pushbuttons, emergency stop actuators, etc.) have the intended tactility, reset and function only when assembled with the appropriate switching elements.

drawings**Dimensioned drawing****Mounting hole drawing**