



H
G
F
E
D
C
B
A



Note:


1. Material:

Box: Fibreboard, Corrugated, Double Wall.
Tape: Polystyrene, Heat-Resistant Temperature: 120°C, Color: Black.
Reel: Polystyrene, Heat-Resistant Temperature: 70°C, Color: Blue.
Bag: Polyethylene, Heat-Resistant Temperature: 100°C.

2. Peeling Strength: 0.1 ~ 1.3 N (10 ~ 130 Grams)

3. Peeling Speed: 300 mm/min.

4. Each bag includes desiccant.



DETAIL 1
4:1

Product no.	PCS/Reel	Reels/Carton	PCS/Carton
USB1110	350	8	2800

Part Number USB1110		Product Description USB 3.0 Receptacle, Full Size, Type A, Mid-Bottom Mount, Horizontal, Through-Hole	
Drawing Date 20th February 2013			
By CC	Drawing Release	Tolerances (Except as Noted) Length: X. ± 0.50 X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10	Units: Metric (mm) 3rd Angle Projection
Detail	A5	± 2°	
Revision	10/10/25		
Date			
		RoHS COMPLIANT 2011/65/EU Deca-SIDE	
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	
		Not to Scale	
		Drawn By AJO	
		Sheet No. 2/2	

GCT
www.gct.co