


# PRODUCT SPECIFICATION

Part Number	SWT0305	Rev	A	Date	22/07/25
Product Description	Tactile Switch, 6.0 x 6.0mm, Top Actuated, J Lead, SPST- NO			Page	1
Doc Number	SWT0305	Prepared	KY	Checked	CC
				Approved	PH



## Features:

Outline: 6.0 X 6.0mm

Profile Height: 9.5mm

Actuated Orientation: Top Actuated

Lead Type: J Lead

## Specification:

### Material

Housing: PPA, Black.

Button: PPA, Black.

Terminal: Brass.

Contact: Stainless Steel.

Cover: Brass.

### Electrical

Voltage Rating: 12V DC.

Current Rating: 50mA.

Contact Resistance: 100mΩ Max.

Dielectric Withstanding Voltage: 250V AC.

Insulation Resistance: 100MΩ Min.

### Plating

Terminal: Silver Plated.

Contact: Silver Plated.

Cover: Tin Plated.

### Mechanical & Environmental

Operating Temperature: -25C to +85°C


Operating Force: See Ordering Grid.

Travel: 0.25±0.10mm

Durability: 100,000 cycles

Solder Tails Co-planarity: 0.10mm Max.

## Ordering Grid:



# PRODUCT SPECIFICATION

Part Number	SWT0305	Rev	A	Date	22/07/25
Product Description	Tactile Switch, 6.0 x 6.0mm, Top Actuated, J Lead, SPST- NO			Page	2
Doc Number	SWT0305	Prepared	KY	Checked	CC
				Approved	PH

## Reflow Soldering Profile:

Pb-free reflow profile requirements

Parameter	Reference	Specification
Average temperature gradient in preheating		2.5°C/s
Soak time	tsoak	2-3 minutes
Time above 217°C	t1	60 s
Time above 230°C	t2	50 s
Time above 250°C	t3	3 s
Peak temperature in reflow	Tpeak	255°C (-0/+5°C)
Temperature gradient in cooling		Max -5°C/s





Fig. 1.0, this profile is the minimum requirement for evaluating soldering heat resistance of components. Heat transfer method used for reflow soldering is hot air convection. The actual air temperatures used to achieve the specified profile is higher and largely dependent on the reflow equipment.

# PRODUCT SPECIFICATION

Part Number	SWT0305	Rev	A	Date	22/07/25
Product Description	Tactile Switch, 6.0 x 6.0mm, Top Actuated, J Lead, SPST- NO			Page	3
Doc Number	SWT0305	Prepared	KY	Checked	CC
				Approved	PH

## Precaution for Operating:

1. Deviation of operating part from the centre axis of the switch shall be within 0.35mm.
2. Allowable operating angle:  $90^\circ \pm 3^\circ$  degrees.
3. Do not overload and shock the switch.
4. Avoid pressing on the button with sharp objects.
5. Cleaning after product soldering is not allowed.
6. Avoid switching on for a long time.



## Recommended Operating Conditions

## Precaution for Handling and Storage:

1. Products are vacuum sealed in plastic bag with desiccant.
2. Recommended storage conditions: -20 to +50°C, 20% to 85% humidity.
3. Avoid exposing to corrosive gas, direct sunlight.
4. After the packaging is opened, use the products as quickly as possible.
5. Products that have not been used up must be vacuum sealed in plastic bag with desiccant.

# PRODUCT SPECIFICATION

<b>Part Number</b>	SWT0305	<b>Rev</b>	A	<b>Date</b>	22/07/25
<b>Product Description</b>	Tactile Switch, 6.0 x 6.0mm, Top Actuated, J Lead, SPST- NO			<b>Page</b>	4
<b>Doc Number</b>	SWT0305	Prepared	KY	Checked	CC

## Revision details:

Revision	Information	Page	Release Date
0.1	First draft	-	17/06/2025
0.2	Update 3D view	1	02/07/2025
A	First Release	-	22/07/2025

