

General Description

SY205205 is a low-capacitance transient voltage suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for data interfaces. With typical capacitance of 25pF, SY205205 is designed to protect against over-voltage and over-current transient events. It complies with IEC61000-4-2 (ESD) ($\pm 30\text{kV}$ air, $\pm 30\text{kV}$ contact discharge), IEC61000-4-5 (surge) (16A, 8/20 μs).

Each SY205205 device can protect one data line.

Features

- Transient Protection for data Lines
 - IEC61000-4-2 (ESD) $\pm 30\text{kV}$ (air) $\pm 30\text{kV}$ (contact)
 - IEC61000-4-5 (surge) 16A (8/20 μs)
- For Operating Voltage of 3.3V and Below
- Package Optimized for data Lines
- Small Package:
DFN1.0×0.6-2/SOD523/DFN0.6×0.3-2
- Protects One Data Line
- Capacitance: 25pF
- Low Leakage Current $0.01\mu\text{A}$ @ V_{RWM} (typical)
- Low Clamping Voltage
- Each I/O pin withstands over 1000 ESD strikes for $\pm 8\text{kV}$ contact discharge.

Applications

- Portable Electronics
- Desktops, Servers, and Notebooks
- Mobile Phones
- Digital Camera Ports

Mechanical Characteristics

- Package: DFN1.0×0.6-2/SOD523/DFN0.6×0.3-2
- Marking: Device Code, Date code
- Packaging: Tape and Reel


Circuit Diagram




Ordering Information

Part Number	Package Type	Top Mark
SY205205DXC	DFN0.6x0.3-2 RoHS Compliant and Halogen Free	P
SY205205DWC	DFN1.0x0.6-2 RoHS Compliant and Halogen Free	LM
SY205205ANC	SOD523 RoHS Compliant and Halogen Free	LM

Pinout (Top View)



Marking Codes



Note 1: "P", "L" is device code, fixed.

Note 2: "M" is date code, from 1 to 0, A to Z

Absolute Maximum Rating					
Parameter	Symbol	Test Condition	Min	Max	Unit
Maximum Peak Pulse Current (8/20 μ s)	I _{PP}			16	A
Maximum Peak Pulse Power (8/20 μ s)	P _{PK}			155	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}		-30	30	kV
ESD per IEC 61000-4-2 (Contact)					
Operating Temperature	T _{OPT}		-40	+85	°C
Storage Temperature	T _{STG}		-55	+150	°C

Electrical Characteristics T _A = 25°C						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Nominal Reverse Working Voltage	V _{RWM}		-3.3		3..3	V
Reverse Leakage Current @ V _{RWM}	I _R	V _R = 3.3V		0.01	0.1	μA
Reverse Breakdown Voltage @ I _T	V _{t1}	I _T = 10mA	3.7			V
Clamping Voltage @ I _{PP}	V _C (1)	I _{PP} = 16A, t _p = 10/100ns		6		V
Clamping Voltage @ I _{PP}	V _C (1)	I _{PP} = 16A, t _p = 8/20 μ s			10	V
Dynamic Resistance	R _{DYN} (1,2)	t _p = 10/100ns		0.17		Ω
Parasitic Capacitance	C _{ESD} (1)	V _R = 0V, f = 1MHz	25		30	pF

Note 1: The device is not guaranteed to function outside its operating conditions.

Note 2: R_{DYN} calculated based on I_{PP}=8A to I_{PP}=16A, t_p = 10/100ns.






Figure 1. Bi-Directional TVS

Typical Characteristics


TLP Testing of I/O to I/O




Capacitance vs. Voltage of I/O to I/O




Pulse Waveform




Clamping Voltage vs. Peak Pulse Current (8/20μs)



ESD Clamping of I/O to I/O (+8kV Contact per IEC 61000-4-2)



ESD Clamping of I/O to I/O (-8kV Contact per IEC 61000-4-2)



Application Information

The SY205205 protects one bidirectional data line against over-voltage and over-current transient events by clamping it to an acceptable reference.

The SY205205 pin connections are shown in Figure 2. The protected line is connected at Pin1 while Pin2 is connected to GND, which should connect to a ground plane on the board. All path lengths connected to pins of SY205205 should be as short as possible to minimize the parasitic inductance.







Figure 2. ESD/Surge Protection Circuit


PCB Layout Guidelines

For optimum ESD protection and circuit performance, the following circuit board guidelines are recommended:

- Place SY205205 as close to the connector or terminal ports as possible.
- Use a large via to connect the SY205205 pin to the ground.
- Avoid running signals near board edges.
- The SY205205 should be placed near the protected line.
- The distance between the SY205205 ground pin and the GND reference path should be as short as possible.


DFN1.0x0.6-2 Package Outline

Top View
Side View

Bottom View
Detail A

**Recommended PCB Layout
(Reference only)**

Note: All dimensions are in millimeters and exclude mold flash and metal burr.


DFN0.6x0.3-2 Package Outline


Note: All dimensions are in millimeters and exclude mold flash and metal burr.


SOD 523 Package Outline




Top View



Side View



Side View




**Recommended PCB Layout
(Reference only)**


Note: All dimensions are in millimeters and exclude mold flash and metal burr.

Tape and Reel Specification


DFN1.0x0.6-2 Taping Orientation




DFN0.6x0.3-2 Taping Orientation



SOD523 Taping Orientation



Carrier Tape & Reel Specification for Packages



Package Types	Tape Width (mm)	Pocket Pitch(mm)	Reel Size (Inch)	Qty per Reel (pcs)
DFN1.0x0.6-2	8	2	7"	10000
DFN0.6x0.3-2	8	2	7"	10000
SOD523	8	2	7"	8000

Revision History

The revision history provided is for informational purpose only and is believed to be accurate, however, not warranted. Please make sure that you have the latest revision.

Revision Number	Revision Date	Description	Pages changed
0.9	08/29/2019	Initial Release	
1.0	08/29/2020	Production Release	
1.0A	11/8/2023	V_{t1} min changed from 3.4V to 3.7V	2

IMPORTANT NOTICE

1. Right to make changes. Silergy and its subsidiaries (hereafter Silergy) reserve the right to change any information published in this document, including but not limited to circuitry, specification and/or product design, manufacturing or descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to Silergy's standard terms and conditions of sale.

2. Applications. Application examples that are described herein for any of these products are for illustrative purposes only. Silergy makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Buyers are responsible for the design and operation of their applications and products using Silergy products. Silergy or its subsidiaries assume no liability for any application assistance or designs of customer products. It is customer's sole responsibility to determine whether the Silergy product is suitable and fit for the customer's applications and products planned. To minimize the risks associated with customer's products and applications, customer should provide adequate design and operating safeguards. Customer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Silergy assumes no liability related to any default, damage, costs or problem in the customer's applications or products, or the application or use by customer's third-party buyers. Customer will fully indemnify Silergy, its subsidiaries, and their representatives against any damages arising out of the use of any Silergy components in safety-critical applications. It is also buyers' sole responsibility to warrant and guarantee that any intellectual property rights of a third party are not infringed upon when integrating Silergy products into any application. Silergy assumes no responsibility for any said applications or for any use of any circuitry other than circuitry entirely embodied in a Silergy product.

3. Limited warranty and liability. Information furnished by Silergy in this document is believed to be accurate and reliable. However, Silergy makes no representation or warranty, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. In no event shall Silergy be liable for any indirect, incidental, punitive, special or consequential damages, including but not limited to lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges, whether or not such damages are based on tort or negligence, warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Silergy' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Standard Terms and Conditions of Sale of Silergy.

4. Suitability for use. Customer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Silergy components in its applications, notwithstanding any applications-related information or support that may be provided by Silergy. Silergy products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Silergy product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Silergy assumes no liability for inclusion and/or use of Silergy products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

5. Terms and conditions of commercial sale. Silergy products are sold subject to the standard terms and conditions of commercial sale, as published at <http://www.silergy.com/stdterms>, unless otherwise agreed in a valid written individual agreement specifically agreed to in writing by an authorized officer of Silergy. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Silergy hereby expressly objects to and denies the application of any customer's general terms and conditions with regard to the purchase of Silergy products by the customer.

6. No offer to sell or license. Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights. Silergy makes no representation or warranty that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right. Information published by Silergy regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from Silergy under the patents or other intellectual property of Silergy.

For more information, please visit: www.silergy.com

© 2023 Silergy Corp.

All Rights Reserved.