


Plastic Shell w/ Strain Relief



Material and Finish

Body: ABS thermoplastic,
UL94HB Rated, black

Contacts: copper alloy,
silver plated

Insert Material: Nylon,
UL94V-2 Rated

Shield: nickel plated
iron sheet

Electrical Characteristics

Insulation Resistance:
50 Megohms min. at 250V DC

Dielectric Withstanding Voltage:
500V AC RMS for 1 minute

Contact Current Rating:
24V DC, 2.5 Amp max.

Mechanical Characteristics


Durability Test: 500 cycles min.

Insertion Force: 5kg max.


Extraction Force: 1.0kg-5.0kg

Operating Temperature: -25°C to +80°C

Pin Block



Socket Configuration (KQLAX-xP Series)



Tolerances

X.X ± 0.25
X.XX ± 0.15
Unless Stated
Otherwise

RoHS COMPLIANT

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	9/6/05	New Drawing	R. Aguirre	H. MA	R. Aguirre	8/16/05
A2	9/13/06	ECO #06-039	R. Aguirre	H. MA		
A3	04/12/18	Update Address & RoHS Logo	J. Elbanna	C. Furumasu	UNITS	mm
A4	02/22/19	ECO #19-018	G. Serrato	D. Shehan		

KQLAX-xP

x = number of contacts

Circular Male Connector, RoHS Compliant

Cable Mount, Quick Lock Type

