

Description

The AH9247 is a high sensitivity Hall-effect switch with internal pullup resistor on the output, designed for battery-operation, handheld equipments.


A chopper stabilized amplifier improves stability of magnetic switch points. A sleep-awake logic controls the IC in sleep time or awake time. This function will reduce the average operating current of the IC. During the awake time, the output is changed with the magnetic flux density. During the sleep time, the output is latched in its previous state and the current consumption will reduce to some μ A.

The output can be switched on with either north or south pole of sufficient strength. If the magnetic flux density perpendicular to the part marking surface is larger than operating point (B_{OP}), the output will be turned on; if it is less than releasing point (B_{RP}), the output will be turned off.

The AH9247 is available in TO92S (TYPE B), SC59 and DFN-2X2-3 packages which are optimized for most applications.


Pin Assignments

(Front View)



TO92S (TYPE B)

(Top View)



SC59

DFN-2X2-3

Features

- Micropower Operation
- 2.5V to 5.5V Power Supply
- Switching for Both Poles of a Magnet (Omnipolar)
- Stabilized Chopper
- Superior Temperature Stability
- Digital Output Signal
- Built-in Pullup Resistor
- ESD (HBM): 6000V
- Small Low Profile DFN-2X2-3, Industry-Standard SC59 and TO92S (TYPE B) Packages
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.**

<https://www.diodes.com/quality/product-definitions/>


Applications

- Cover switches in notebook PC/PDA
- Handheld wireless application awake switches
- Magnet switches in low duty-cycle applications

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


Typical Applications Circuit



Pin Descriptions

Pin Number			Pin Name	Function
TO92S (TYPE B)	SC59	DFN-2X2-3		
1	1	1	VCC	Power supply pin
2	3	3	GND	Ground pin
3	2	2	OUTPUT	Output pin

Functional Block Diagram



A (B)

A for TO92S (TYPE B)

B for SC59 and DFN-2X2-3

Absolute Maximum Ratings (@ $T_A=+25^\circ\text{C}$, Note 4)

Symbol	Parameter	Rating		Unit
V _{CC}	Supply Voltage	7		V
I _{CC}	Supply Current (Fault)	6		mA
V _{OUT}	Output Voltage	7		V
I _{OUT}	Output Current	2		mA
B	Magnetic Flux Density	Unlimited		Gauss
P _D	Power Dissipation	TO92S (TYPE B)	400	mW
		SC59	230	
		DFN-2X2-3	230	
T _{STG}	Storage Temperature	-55 to +150		°C
T _J	Junction Temperature	+150		°C
—	ESD (Human Body Model) (Note 5)	6000		V
—	ESD (Machine Model) (Note 5)	400		V

Notes:

- Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.
- Electronic semiconductor products are sensitive to Electro Static Discharge (ESD). Always observe Electro Static Discharge control procedures whenever handling semiconductor products.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{CC}	Supply Voltage	2.5	5.5	V
T _{OP}	Operating Temperature	-40	+85	°C

Electrical Characteristics (@ $T_A=+25^\circ\text{C}$, V_{CC}=3V, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V _{CC}	Supply Voltage	Operating	2.5	3	5.5	V
I _{AW}	Supply Current	Awake	—	1.8	3	mA
I _{SL}		Sleep	—	4	10	μA
I _{AVG}		Average	—	8	15	μA
I _{OUT}	Output Current	—	—	—	1.0	mA
V _{SAT}	Saturation Voltage	I _{OUT} =1.0mA	—	—	0.4	V
t _{AW}	Awake Mode Time	Operating	—	120	—	μs
t _{SL}	Sleep Mode Time	Operating	—	80	120	ms
D	Duty Cycle	—	—	0.15	—	%
f _C	Chopper Frequency	—	—	15	—	kHz

Magnetic Characteristics (@ $T_A=+25^\circ\text{C}$, $V_{CC}=3\text{V}$, unless otherwise specified. Note 6)


For TO92S (TYPE B) Package

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
B _{OPS} (South Pole to Part Marking Side)	Operating Point	B>B _{OPS} , V _{OUT} =low(output on)	15	30	55	Gauss
B _{OPN} (North Pole to Part Marking Side)		B>B _{OPN} , V _{OUT} =low(output on)	-55	-30	-15	Gauss
B _{RPS} (South Pole to Part Marking Side)	Releasing Point	B<B _{RPS} , V _{OUT} =high(output off)	5	20	45	Gauss
B _{RPN} (North Pole to Part Marking Side)		B<B _{RPN} , V _{OUT} =high(output off)	-45	-20	-5	Gauss
B _{HYS}	Hysteresis	B _{OPX} - B _{RPX} (Note 7)	—	10	—	Gauss


For SC59 and DFN-2X2-3 Packages

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
B _{OPS} (South Pole to Part Marking Side)	Operating Point	B>B _{OPS} , V _{OUT} =low(output on)	20	30	40	Gauss
B _{OPN} (North Pole to Part Marking Side)		B>B _{OPN} , V _{OUT} =low(output on)	-40	-30	-20	Gauss
B _{RPS} (South Pole to Part Marking Side)	Releasing Point	B<B _{RPS} , V _{OUT} =high(output off)	5	20	32	Gauss
B _{RPN} (North Pole to Part Marking Side)		B<B _{RPN} , V _{OUT} =high(output off)	-32	-20	-5	Gauss
B _{HYS}	Hysteresis	B _{OPX} - B _{RPX} (Note 7)	—	10	—	Gauss

Notes: 6. The specifications stated here are guaranteed by design. 1 Gauss=0.1mT
 7. B_{OPX}=operating point (output turns on); B_{RPX}=releasing point (output turns off)



Output Voltage vs. Magnetic Flux Density

Test Conditions




Average Supply Current (Notes 8 and 9)

Note 8: I_{CC} represents the average supply current. OUTPUT is open during measurement.
 Note 9: The device is put under magnetic field with $B < B_{RP}$.



Output Saturation Voltage (Notes 10 and 11)

Note 10: The output saturation voltage V_{SAT} is measured at $V_{CC}=2.5V$ and $V_{CC}=5.5V$.
 Note 11: The device is put under magnetic field with $B > B_{OP}$.




Magnetic Thresholds (Notes 12 and 13)


Note 12: B_{OP} is determined by putting the device under magnetic field swept from $B_{OP(min)}$ to $B_{OP(max)}$ until the output is switched on.
 Note 13: B_{RP} is determined by putting the device under magnetic field swept from $B_{OP(max)}$ to $B_{RP(min)}$ until the output is switched off.

Performance Characteristics


B_{OP}/B_{RP} vs. Supply Voltage




B_{OP}/B_{RP} vs. Ambient Temperature




Average Supply Current vs. Supply Voltage




Awake Mode Time vs. Supply Voltage




Sleep Mode Time vs. Supply Voltage



Power Dissipation vs. Ambient Temperature




Ordering Information



Part Number	Status	Package	Package Code	Packing	
				Qty.	Carrier
AH9247Z3-G1	Active	TO92S (TYPE B)	Z3	1000	Bulk
AH9247DNTR-G1	EOL (Note 14)	DFN-2X2-3	DN	3000	7" Tape & Reel


Note 14: the AH9247DNTR-G1 is obsolete. please [CONTACT US](#).



Part Number	Status	Package	Package Code	Packing	
				Qty.	Carrier
AH9247-W-7	Active	SC59	W	3000	7" Tape & Reel


Marking Information

(1) Package Type: TO92S (TYPE B)




Part Number	Package	Identification Code
AH9247	TO92S (TYPE B)	9247

(2) Package Type: SC59



Part Number	Package	Identification Code
AH9247	SC59	GX8

(3) Package Type: DFN-2X2-3




Part Number	Package	Identification Code
AH9247	DFN-2X2-3	JF

Package Outline Dimensions (All dimensions in mm(inch).)


Please see <http://www.diodes.com/package-outlines.html> for the latest version.

(1) Package Type: TO92S (TYPE B)



TO92S (TYPE B)			
Dim	Min	Max	Typ
A	1.420	1.620	-
A2	-	-	0.750
b	0.360	0.480	-
b2	0.380	0.550	-
c	0.360	0.510	-
D	3.850	4.150	-
E	2.900	3.310	-
e	-	-	1.270
L	14.000	15.500	-
L1	-	-	1.600
θ	44°	46°	-

All Dimensions in mm




Sensor Location

Package Outline Dimensions (All dimensions in mm(inch).) (continued)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(2) Package Type: SC59



SC59			
Dim	Min	Max	Typ
A	0.35	0.50	0.38
B	1.50	1.70	1.60
C	2.70	3.00	2.80
D	-	-	0.95
G	-	-	1.90
H	2.90	3.10	3.00
J	0.013	0.10	0.05
K	1.00	1.30	1.10
L	0.35	0.55	0.40
M	0.10	0.20	0.15
N	0.70	0.80	0.75
α	0°	8°	-

All Dimensions in mm

Min/Max




Sensor Location

Package Outline Dimensions (All dimensions in mm(inch).) (continued)

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


(3) Package Type: DFN-2X2-3



Suggested Pad Layout


Please see <http://www.diodes.com/package-outlines.html> for the latest version.

(1) Package Type: SC59



Dimensions	Value (in mm)
Z	3.4
X	0.8
Y	1.0
C	2.4
E	1.35

(2) Package Type: DFN-2X2-3



Dimensions	Y (mm)/(inch)	X1=X3 (mm)/(inch)	Y1 (mm)/(inch)	X2 (mm)/(inch)	Y2 (mm)/(inch)	Y3 (mm)/(inch)	E (mm)/(inch)
Value	2.200/0.087	0.400/0.016	0.300/0.012	1.600/0.063	1.100/0.043	0.600/0.024	1.300/0.051

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish – Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 
- Weight: TO92S (TYPE B) – 0.077 grams (Approximate)
SC59 – 0.009 grams (Approximate)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.

© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com