

SiPB-1690

Smart Industrial UPS Board



SiPB-1690A



SiPB-1690B

Features

- Long-term availability and value-added services
- Backup time including safe shutdown
- Support power input : 12V/24V
- Normal mode power output: 12V//24V (based on input voltage)
Backup mode power output: 12V/24V via jumper
- Wide operating temperature range (-20°C to 70°C)
- System monitoring for powered device(PD)
- Reboot function for PC-based systems

System

Chip High Current Super CAP Backup Controller

Supercapacitor

Capacity 100 Farads / each

Power Requirement

Power Input DC +12/24V input

Output voltage backup mode DC +12V/24V, selectable via jumper

Output voltage normal mode DC ±12V/24V

Output power Max. 60W

Power Management Powered device reboot via software

I/O

Power Input 1 x Power in, ATX-4 connector

Power Output 1 x Power out, ATX-2 connector

Switch for Power Output 1 x Jumper

USB 1 x 4-pin box header

Environmental

Operating Temp. -20°C ~ 70°C (-4°F ~ 140°F)

Storage Temp. -30°C ~ 80°C (-22°F ~ 158°F)

Operating Humidity 10 ~ 95% RH @ 70°C (non-condensing)

Mechanical

Weight SiPB-1690A: 185g (0.41lb)
SiPB-1690B: 285g (0.63lb)

Dimensions SiPB-1690A: 160 x 88 x 22.2 mm
(W x H x D) SiPB-1690B: 160 x 88 x 44.7 mm

Nominal backup time, measured at +25 °C

SiPB-1690A 30W ~ 33sec ; 60W ~ 16sec

SiPB-1690B 30W ~ 66sec ; 60W ~ 32sec

OS Support


Windows 7/10/11

Ordering Information


SiPB-1690A 4S1P, 4 x100F Smart Industrial UPS Board

SiPB-1690B 4S2P, 8 x100F Smart Industrial UPS Board

Note: To download device driver and SiP Management Utility, please visit the product page on ARBOR website.



Dimensions



Backup Time vs Load Chart

