

AANI-CH-0029

Request Samples



Check Inventory



3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = N/A



Features


- Compact Size: 3.2 x 2.5 x 2.0 mm
- Center Frequency: 13.56 MHz
- Nominal Inductance: 7 uH
- Read Distance: 10 ~ 30 mm
- Fully SMD compatible
- RoHS Compliant

Applications

- RFID / NFC Systems
- Data Transfer and Pairing
- Access Control and Identification
- Payment, EMVCo
- Phones, Infotainment, POS Terminals

Product Image





AANI-CH-0029

Request Samples



Check Inventory



3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
 MSL Level = N/A

Electrical Specification

Parameter	Specification	Unit
Operating Frequency	13.56	MHz
Bandwidth	1	MHz
VSWR (Typ.)	1.6	
Inductance	7	$\mu\text{H}@13.56\text{MHz}$
Q-Factor	11.3	
DC Resistance	52.75	$\Omega@13.56\text{MHz}$
Self-Resonance Frequency	61.13	MHz
Reading Distance	10~30	mm
Polarization	Linear	-
Impedance	50	Ω


Mechanical Specification

Parameter	Specification
Dimension	3.2 x 2.5 x 2.0 mm
Mounting Type	Surface Mount
Weight	0.05g

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +105°C
Storage Temperature	-40°C to +85°C
Humidity	85% R.H.
RoHS Compliance	Yes

NFC Chip Antenna



AANI-CH-0029

Request Samples




Check Inventory



3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Ordering Information

Part Number	Description
AANI-CH-0029	NFC Chip Antenna on Cut Tape
AANI-CH-0029-T	NFC Chip Antenna on Tape & Reel



AANI-CH-0029

Request Samples




Check Inventory




3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
 MSL Level = N/A


Product Dimensions




FRONT VIEW




SIDE VIEW



BOTTOM VIEW



Unit: inches[mm]



AANI-CH-0029

Request Samples




Check Inventory




3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Land Pattern



Unit: inches[mm]



AANI-CH-0029

Request Samples



Check Inventory



3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process
Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2


Pb-Free Process
Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	200°C
Time (T_{smin} to T_{smax}) (t_s)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T_p)*	see Table 1	see Table 2
Time (t_p)** within 5°C of the specified classification temperature (T_c)	20 sec.	30 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as supplier minimum and a user maximum.



AANI-CH-0029

Request Samples



Check Inventory




3.2 x 2.5 x 2.0 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Packaging

Tape & Reel

1. Tape & Reel Dimension



Carrier Tape Specifications (mm)

E1	D0	P0	P2	K0	P1	W	A0	B0	Reel Qty
1.75	1.5	4.0	2.0	2.25	8.0	12	2.85	3.60	3,000

Reel Specifications (mm)

A	W ₁	N
330	13	100

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.