

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory



40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Features

- Frequency Range: 698-960 / 1710-2690 MHz
- Compact & Low-Profile
- Peak Gain: 1.0 / 5.9 dBi
- Efficiency: 66 % / 80 %
- Surface Mount (SMD)

Applications

- Internet of Things (IoT) Devices
- LTE-M, Cat M, Cat M1, NB-IoT
- LTE CAT 1 up to CAT 20 Supported
- Smart Home Networking
- Networking & Telecommunication

Product Image



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory



40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Electrical Specification

Parameter	Specification		Unit
Operating Frequency	698-960	1710-2690	MHz
Return Loss	< -7.0	< -9.5	dB
VSWR (Typ.)	< 2.6	< 2.0	:1
Peak Gain	1.0	5.9	dBi
Average Gain	0.25	3.75	
Minimum Total Efficiency	-2.9 (51)	-2.8 (53)	dB (%)
Average Total Efficiency	-2.3 (59)	-2.2 (60)	
Maximum Total Efficiency	-1.8 (66)	-1.0 (80)	
Impedance	50		Ω
Polarization	Linear		-
Radiation Pattern (Azimuth)	Omni-directional		-
Input Power	< 5		W

Note : All test measurements were conducted on 135 x 40 mm. Performance of the chip antenna will vary relative to the ground plane size in use.

Mechanical Specification

Parameter	Specification
Dimensions	40 x 7 x 3 mm
Mounting Type	Surface Mount
Antenna Clearance Space	40 x 14.7 mm
Evaluation Board size	135 x 40 mm
Solder Termination	Ag (Environmental-Friendly Pb-Free)

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
Relative Humidity	90% to 95%
MSL Level	1
RoHS Complaint	Yes



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory



40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Ordering Information

Part Number	Description
AANI-CH-0202	Low Profile SMD LTE Chip Antenna on Cut Tape
AANI-CH-0202-T	Low Profile SMD LTE Chip Antenna on Tape & Reel
AANI-CH-0202-EVB	Low Profile SMD LTE Chip Antenna Evaluation Board



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Product Dimensions



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Evaluation Board Dimensions



Unit: mm

No.	Description
1	Antenna 40 x 7 x 3 mm
2	PCB 135 x 40 x 1 mm

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Measurement Setup photo



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory





40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Reflection Characteristics –Return Loss & VSWR



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics – Peak Gain



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics – Total Efficiency (%)



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Radiation Characteristics – 3D & 2D Pattern

698MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

960MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

1710MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

1990MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory






40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

2500MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory







40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

2690MHz



Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1



Evaluation Board Outline & Matching Circuit

The evaluation board is developed to showcase the performance of this chip antenna on a typical PCB and to simplify antenna testing and evaluation. It has a size of 135 x 40 mm. The performance could vary with different PCB sizes and Abracon can offer support to optimize the antenna for your specific application.




FOOTPRINT SOLDER PADS WITH PCB OUTLINE
SCALE 2:1

PIN	DESCRIPTION
1	PAD
2	Feed
3	GND
4	PAD



GROUND CLEARANCE BOTTOM VIEW
(SILKSCREEN NOT SHOW)



GROUND CLEARANCE TOP VIEW
(SILKSCREEN NOT SHOW)

The evaluation board has a matching circuit implemented next to the antenna. This is aimed to enable optimization possibilities for the user.

The standard tuning for the evaluation board is the following (can be replaced by equivalent):


However, it is common that the resonant frequency will shift during implementation in an arbitrary device. Therefore, this matching may be changed with other values/components/brands for compensation of such effects.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED



Low Profile SMD LTE Chip Antenna

AANI-CH-0202


Request Samples



Check Inventory



40 x 7 x 3 mm
RoHS/RoHS II Compliant
MSL Level = 1



Matching circuit

Location	X1	X2	X3	X4
Description	0.5pF	3.3nH	N/A	6.8nH
Part Number	0402N0R5A500CT	AIMC-0402-3N3ST	N/A	AIMC-0402-6N8ST
Manufacturer	WALSIN TECHNOLOGY	ABRACON	N/A	ABRACON



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant


MSL Level = 1

Recommended PCB layout

If there are several layers in the PCB, there is an advantage to add vias for smooth interconnection of the ground areas to avoid splits in the ground plane. It is also important that the ground clearance is respected through **all layers** of the PCB. It is recommended to implement a matching network to optimize the antenna impedance in your application.



Detailed view of antenna pads and antenna extension trace:



Unit: mm



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory



40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Reflow Profile [JEDEC J-STD-020]

Solder paste: Sn/3.0Ag/0.5Cu




Table 1

SnPb Eutectic Process

Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5mm	235°C	220°C
≥2.5mm	220°C	220°C

Table 2

Pb-Free Process

Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6mm	260°C	260°C	260°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{min})	100°C	150°C
Temperature maximum (T_{max})	150°C	200°C
Time (T_{min} to T_{max}) (t_s)	60 – 120 sec.	60 – 90 sec.
Average ramp-up rate (T_{max} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	217°C
Time at Liquidous (T_L)	60 – 150 sec.	60 – 150 sec.
Peak package body temperature (T_p)*	See Table 1	See Table 2
Time (T_p)* within 5°C of the specified classification temperature (T_c)	20 sec.	10 sec.
Ramp-down rate (T_p to T_{max})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Low Profile SMD LTE Chip Antenna



AANI-CH-0202

Request Samples



Check Inventory




40 x 7 x 3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Packaging

Tape & Reel Dimension



Carrier Tape Specifications (mm)

Do	K ₀	E ₁	P ₀	P ₂	T	F	P ₁	W	A ₀	B ₀	Reel Qty
1.50 ± 0.1	3.80 ± 0.1	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.10	0.3 ± 0.05	26.2 ± 0.10	12.0 ± 0.1	56.0 ± 0.10	7.3 ± 0.1	41 ± 0.1	1,000

Reel Specifications (mm)

A	W ₁	N	B	C	D
330 ± 1.0	62 ± 1.0	100 ± 1.0	2.0 ± 0.5	13 ± 0.5	20.2 min

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 08-20-25

ABRACON IS
ISO9001-2015
CERTIFIED