


SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory



1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1


Features

- AEC-Q200 Qualified
- GPS/GLONASS/BEIDOU/GALILEO Support
- Bandwidth 46.834MHz
- Small Form Factor 1.1 x 0.9 x 0.44 mm
- Low Insertion Loss: 1.3 dB
- Maximum Input Power: 15 dBm
- RoHS Compliant


Applications

- RF Modules
- RTK Systems
- Automotive Transportation & Telematics
- Asset Tracking / Fleet Management
- UAVs, Robotics & Autonomous Vehicles
- Micro-Mobility Solutions
- Precision Agriculture

Product Image



SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory



1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1


Electrical Specification

Parameters	Minimum	Typical	Maximum	Units	Notes
Center Frequency (fc)	-	1582.469	-	MHz	-
VSWR ⁽¹⁾	-	1.5	1.7	-	1559.052 - 1605.886MHz
Insertion Loss ⁽¹⁾	-	1.6	1.8	dB	1559.052 – 1563.144 MHz (B1I)
	-	1.6	1.8		1565.42 – 1585.42 MHz (L1 BW 20MHz)
	-	1.0	1.4		1574.39 – 1576.45 MHz (L1 BW 2MHz)
	-	1.4	2.1		1597.552 - 1605.886 MHz (G1)
Amplitude Ripple ⁽¹⁾	-	0.24	0.5	dB	1559.052 - 1605.886 MHz
Attenuation ⁽¹⁾ (Reference level from 0 dB)	37	40	-	dB	10 - 960 MHz
	42	46	-		1427- 1463 MHz
	38	42	-		1710 - 1797 MHz
	37	41	-		1850 - 1980 MHz
	37	40	-		2010 - 2025 MHz
	40	44	-		2305 - 2315 MHz
	41	45	-		2401 - 2483 MHz
	42	46	-		2500 - 2570 MHz
	22	31	-		5160 - 5885 MHz
Group Delay ⁽¹⁾ (+25 °C)	-	12	19	ns	1559 - 1605 MHz
Source Impedance ⁽²⁾ (single ended)	-	50	-	Ω	-
Load Impedance ⁽²⁾ (single ended)	-	50	-	Ω	-
Input Power Level	-	-	15	dBm	-
DC Voltage (V)	-	-	5	V	-

Notes: (1) Averaged values of linear S-Parameters at +25°C

(2) A matching network is unnecessary (refer to the Measurement Circuits section)

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory



1.1 x 0.9 x 0.44 mm

RoHS Compliant

MSL Level = 1


Mechanical Specification

Parameters	Specifications
Filter Dimension	1.1 x 0.9 x 0.44 mm
Mounting Type	Surface Mount

Environmental Specification

Parameters	Specifications
Operating Temperature Range	-40°C ~ +105°C
Storage Temperature Range	-40°C ~ +105°C
ESD	50V(MM) / 100V(HBM)
MSL level	1
RoHS Compliant	Yes

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory



1.1 x 0.9 x 0.44 mm

RoHS Compliant


MSL Level = 1

Ordering Information

Part Number	Description
AFII-SW-0071-Q	SMD 1582.469 MHz SAW Filter on Cut Tape
AFII-SW-0071-Q-T	SMD 1582.469 MHz SAW Filter on Tape & Reel
AFII-SW-0071-Q-EVB	SMD 1582.469 MHz SAW Filter Evaluation Board

Note: Other options not listed may be available upon request via [Abracon online support](#)

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory




1.1 x 0.9 x 0.44 mm


RoHS Compliant

MSL Level = 1


Package Dimensions



TOP VIEW




FRONT VIEW




BOTTOM VIEW

PIN #	SYMBOL	FUNCTION
1	IN	INPUT
2	GND	GROUND
3	GND	GROUND
4	OUT	OUTPUT
5	GND	GROUND



Unit: mm

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples




Check Inventory



1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1


Recommended Land Pattern



Unit: mm

Please note: The line width should be designed to achieve a 50-ohm characteristic impedance, depending on the PCB material and thickness. For technical assistance, please contact [Abracon online support](#) through our online support platform

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples




Check Inventory




1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1

Measurement Circuit



Port	Matching Component
Input (Pin 1)	R1: 50 Ω
Output (Pin 4)	R2: 50 Ω

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory





1.1 x 0.9 x 0.44 mm

RoHS Compliant


MSL Level = 1

Frequency Characteristics

S21 narrow band



SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory




1.1 x 0.9 x 0.44 mm


RoHS Compliant

MSL Level = 1


S21 wide band



Group Delay



SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples





Check Inventory




1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1

VSWR (S11 & S22)



SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory




1.1 x 0.9 x 0.44 mm


RoHS Compliant

MSL Level = 1


Smith chart S11 (1559~1605MHz)



Smith chart S22 (1559~1605MHz)



SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory



1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process Classification Temperatures (T_c)

Package Thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5mm	235°C	220°C
$\geq 2.5\text{mm}$	220°C	220°C

Table 2

Pb-Free Process Classification Temperatures (T_c)


Package Thickness	Volume mm^3 <350	Volume mm^3 350-2000	Volume mm^3 >2000
<1.6mm	260°C	260°C	260°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	180°C
Time (T_{smin} to T_{smax}) (t_s)	60 – 120 sec.	60 – 90 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	220°C
Time at Liquidous (T_L)	60 – 150 sec.	50 – 80 sec.
Peak package body temperature (T_p)*	See Table 1	See Table 2
Time (T_p)** within 5°C of the specified classification temperature (T_c)	20 sec.	20 ~ 40 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

SMD 1582.469 MHz SAW Filter



AFII-SW-0071-Q

Request Samples



Check Inventory




1.1 x 0.9 x 0.44 mm
RoHS Compliant
MSL Level = 1

Packaging

Tape & Reel

1. Tape & Reel Dimension



Carrier Tape Specifications (mm)

Do	D ₁	E ₁	P ₀	P ₂	T	F	P ₁	W	A ₀	B ₀	K ₀	Reel Qty
1.5 ± 0.1	0.5 ± 0.05	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.05	0.2 ± 0.05	8.0 ± 0.2	2.0 ± 0.05	8.0 ± 0.2	1.1 ± 0.1	1.3 ± 0.1	0.55 ± 0.05	5,000

Reel Specifications (mm)

A	W ₁	N	C	D	B
180.0 ± 1.0	9.0 ± 0.5	60.0 ± 0.5	13.5 ± 0.5	21.0 ± 0.8	2.0 ± 0.5

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 07-01-25

ABRACON IS
ISO9001-2015
CERTIFIED