

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory



Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Features

- Available with or without LED
- Suitable CAT 5 & 6 cable and UTP
- Comply IEEE 802.3ab
- LAN Magnetic with RJ45
- Suitable for RoHS compliant reflow

Applications

- 10, 100 Base-T LAN
- NIC, LoM and PC

Electrical Specifications

Part Number	Turns Ratio $\pm 5\%$		EMI Fingers	LEDs L/R	Insertion Loss (dB TYP)	Return Loss (dB TYP @100 Ω $\pm$ 15 Ω)			
	TX	RX			1- 65 MHz	1- 10 MHz	10-30 MHz	30-60 MHz	60-80 MHz
ARJ11D-MCSA-LU2	1CT:1	1CT:1CT	Yes	NONE	-1	-20	-16	-12	-10
ARJ11D-MASB-B-A-□MU2	1CT:1CT	1CT:1CT	Yes	Y/G	-1	-20	-16	-12	-10
ARJ11D-MCSC-LU2	1CT:1	1CT:1CT	Yes	NONE	-1	-20	-16	-12	-10
ARJ11D-MDSD-A-B-□LT2	1CT:1	1CT:1	No	G/Y	-1	-20	-16	-12	-10
ARJ11D-MCSD-LT2	1CT:1	1CT:1	Yes	NONE	-1	-20	-16	-12	-10
ARJ11D-MDSE-A-B-□MU2	1CT:1CT	1CT:1CT	No	G/Y	-1	-20	-16	-12	-10
ARJ11D-MASE-A-B-□MU2	1CT:1CT	1CT:1CT	Yes	G/Y	-1	-20	-16	-12	-10
ARJ11D-MDSG-B-A-□MU2	1CT:1CT	1CT:1CT	No	Y/G	-1	-20	-16	-12	-10
ARJ11D-MASG-B-A-□MU2	1CT:1CT	1CT:1CT	Yes	Y/G	-1	-20	-16	-12	-10
ARJ11D-MASG-A-A-□MU2	1CT:1CT	1CT:1CT	Yes	G/G	-1	-20	-16	-12	-10
ARJ11D-MESH-LU2	1CT:1	1CT:1CT	No	NONE	-1	-20	-16	-12	-10
ARJ11D-MDSH-A-B-□LU2	1CT:1	1CT:1CT	No	G/Y	-1	-20	-16	-12	-10
ARJ11D-MASH-B-A-□LU2	1CT:1	1CT:1CT	Yes	Y/G	-1	-20	-16	-12	-10
ARJ11D-MBSJ-A-DA-HLT2	1CT:1	1CT:1	Yes	G/O_G	-1	-20	-16	-12	-10
ARJ11D-MBSK-A-DA-HMU2	1CT:1CT	1CT:1CT	Yes	G/O_G	-1	-20	-16	-12	-10
ARJ11D-MBSK-A-B-IMU2	1CT:1CT	1CT:1CT	Yes	G/Y	-1	-20	-16	-12	-10
ARJ11D-MBSL-A-DA-HLU2	1CT:1	1CT:1CT	Yes	G/O_G	-1	-20	-16	-12	-10



12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory



Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Part Number	Crosstalk (dB TYP)			Common Mode Rejection (dB TYP)		Hipot (Vrms) @60Hz
	1-30 MHz	30-60 MHz	60-100 MHz	1-50 MHz	50-150 MHz	
ARJ11D-MCSA-LU2	-40	-35	-30	-30	-20	1500
ARJ11D-MASB-B-A-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MCSC-LU2	-40	-35	-30	-30	-20	1500
ARJ11D-MDSD-A-B-□LT2	-40	-35	-30	-30	-20	1500
ARJ11D-MCSD-LT2	-40	-35	-30	-30	-20	1500
ARJ11D-MDSE-A-B-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MASE-A-B-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MDSG-B-A-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MASG-B-A-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MASG-A-A-□MU2	-40	-35	-30	-30	-20	1500
ARJ11D-MESH-LU2	-40	-35	-30	-30	-20	1500
ARJ11D-MDSH-A-B-□LU2	-40	-35	-30	-30	-20	1500
ARJ11D-MASH-B-A-□LU2	-40	-35	-30	-30	-20	1500
ARJ11D-MBSJ-A-DA-HLT2	-40	-35	-30	-30	-20	1500
ARJ11D-MBSK-A-DA-HMU2	-40	-35	-30	-30	-20	1500
ARJ11D-MBSK-A-B-IMU2	-40	-35	-30	-30	-20	1500
ARJ11D-MBSL-A-DA-HLU2	-40	-35	-30	-30	-20	1500

□: LED Polarity Option

ARJ11D-MA: E, F or G

ARJ11D-MD: E, F or G

Contact Abracon for more custom configurations. See options to build a custom configuration.



12117 Bee Caves Rd, Bldg-3, Suite 200

Bee Cave, TX 78738

Phone: 512-371-6159 Fax: 512-351-8858

For terms and conditions of sales, please visit:

www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory



Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Environmental Specifications


- Storage Temp: -40°C TO +85°C.
- Operating Temp: 0°C TO +70°C.
- ARJ11D Series is **RoHS Compliant**. Operating life: 750 Cycles min.

Part Identification

ARJ11D - - - -

Mechanical	Schematic	Left LED color (e.g. B for Yellow, AB for Green - Yellow)	Right LED color (e.g. B for Yellow, AB for Green - Yellow)	LED polarity	Turns Ratio (Tx)	Turns Ratio (Rx)	Gold plating
MA ~ ME (Please see mechanical section)	SA ~ SR (Please see schematic section)			Blank: No LED	K: 1CT:1.41	S: 1CT:1.41	1: 3u “
				E ~ I (Please see LED polarity section)	L: 1CT:1	T: 1CT:1	2: 6u “
		Blank: No LED	Blank: No LED		M: 1CT:1CT	U: 1CT:1CT	3: 15u “
		A: Green	A: Green		N: 1.414:1CT	V: 1.414:1CT	4: 30u “
		B: Yellow	B: Yellow		O: 1CT:1.41CT	W: 1CT:1.41CT	5: 50u “
		C: Amber	C: Amber		P: 1:2CT	X: 1:2CT	
		D: Orange	D: Orange		Q: 1:1.414CT	Y: 1:1.414CT	
					R: 1CT:2.5	Z: 1CT:2.5	

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory



Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Materials

ARJ11D-MA/MC/MD/ME only:

- Housing Material:**
MATERIAL: NYLON GF (Fr50) UL94V-0
STANDARD COLOR: BLACK
- Insert Material:**
MATERIAL: Phos-Bronze C5210 EH---0.35mm Thickness
Insert -PBT GF UL94V-0
PLATING (1) NICKEL
PLATING (2) 100%Sn
PLATING (3) GOLD (3u " ~50u ") (see options)
- Plate Material:**
PBT GF UL 94V-0
- Contact pin Material:**
MATERIAL: Phos-Bronze C5191---0.35mm Thickness
1.PLATING (1) NICKEL
2.PLATING (2) 100%Sn
- Shielding Material:**
BRASS C2680 PLATING NICKEL

ARJ11D-MB only:

- Housing Material:**
MATERIAL: NYLON GF (Fr50) UL94V-0
STANDARD COLOR: BLACK
- Insert Material:**
MATERIAL: Phos-Bronze C5210 EH---0.35mm Thickness
Insert -PBT GF UL94V-0
PLATING (1) NICKEL
PLATING (2) 100%Sn
PLATING (3) GOLD (3u " ~50u ") (see options)
- Contact pin Material:**
MATERIAL: Phos-Bronze C5191---0.35mm Thickness
1.PLATING (1) NICKEL
2.PLATING (2) 100%Sn
- Shielding Material:**
BRASS C2680 PLATING NICKEL

Note: No material substitutions allowed without prior approval by customers in writing

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A


Mechanical Dimensions

MA







Suggested PCB Layout (Component Side)


MB



PC Board Layout
Component Side Shown




MC







PC Board Layout
Component Side Shown

MD



SUGGESTED PCB LAYOUT




12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes



RoHS/RoHS II Compliant

MSL Level = N/A

ME



PC Board Layout
Component Side Shown



Dimension: mm. All tolerances are ± 0.25 unless otherwise specified



12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Schematics



12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples












Check Inventory



Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A



12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes

RoHS/RoHS II Compliant


MSL Level = N/A

LED polarity


E




F




G



H




I



J



RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes

RoHS/RoHS II Compliant

MSL Level = N/A

Reflow Profile



—— PIN TEMPERATURE

A. Preheating B. Soldering C. Gradual Cooling

Zone	Description	Temperature	Times
1	Preheat	150°C ~ 180°C	60 ~ 120 sec.
2	Peak heat	Tp 250°C±10°C	5 sec. MAX

Ref.

Solder paste: Sn/3.0Ag/0.5Cu

Ramp up rate: 3°C/s Max.

Ramp down rate: 6°C/s Max.




12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED

RJ45 10/100 Base-T Jack with Magnetic Module



ARJ11D Series

Request Samples



Check Inventory




Various sizes

RoHS/RoHS II Compliant


MSL Level = N/A

Packing

2.0 Packing: 60pcs/tray
Packaging material: PET



Outer carton unit : 1080 pcs/ 18 Trays/box



Dimensions: cm



12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/26/2025

ABRACON IS
ISO9001-2015
CERTIFIED