

Precision Ultra Low Phase Noise OCXO in 25x25 mm Package

**ESD Sensitive****25.4 x 25.4 x 12 mm**
Datasheet #456830

Features

- Compact 25 x 25 mm package
- SC-Cut crystal
- High Stability: ± 20 ppb over Operating Temperature Range
- Low Aging: 0.1 ppm 1st year
- Ultra Low Phase Noise floor (-175d Bc/Hz max at 100 kHz)
- Sine wave output

Applications

- Cellular Infrastructure; Base stations
- Test and measurement equipment
- Timing and frequency references
- Battery Powered Equipment
- Tele/Data Communications
- Precision GPS

Absolute Maximum Ratings

Parameters	Symbol	Condition	Min	Typ	Max	Unit	Notes
Input Break Down Voltage	Vcc	5 V supply	-0.5		5.5	V	
Storage temperature	Ts		-55		+105	°C	
Control Voltage	Vc		-1		5.5	V	

Precision Ultra Low Phase Noise OCXO in 25x25 mm Package



ESD Sensitive

25.4 x 25.4 x 12 mm

Datasheet #456830

Electrical ⁽¹⁾

Parameters	Symbol	Condition	Min	Typ	Max	Unit	Notes
Frequency	F			100.00		MHz	
Frequency Tolerance	ΔF	Initial Tolerance	-0.2		+0.2	ppm	@25°C
Operating Temperature Range	OTR		-40		+85	°C	
Frequency Stability	$\Delta F/F$	vs. Temp.	-30		+30	ppb	
		vs. Supply	-3		+3	ppb/5%Vcc	
		vs. Load	-3		+3	ppb/5% load	
Aging		per day per year, first year ten years	-1E-9 -1E-7 -6E-7		+1E-9 +1E-7 +6E-7		after 30 days of continuous operation
Short Term Stability (Allan Deviation)		1s			2E-11		
SSB Phase Noise (achieved after 10 minutes warm-up)	S _φ	1 Hz		-75	-70	dBc/Hz	
		10 Hz		-110	-105		
		100 Hz		-140	-135		
		1 KHz		-165	-160		
		10 KHz		-176	-171		
		100 KHz		-180	-175		
		1 MHz		-180	-175		
Input Voltage	Vcc		4.75	5.0	5.25	V	
Stead State Current	I _{dd}	steady state, 25°C			400	mA	
Warm Up Current					800	mA	
Warm Up Time					2.5	Minutes	@25°C, within ±100 ppb of final frequency after powered on for 1 hour
					15	Minutes	@25°C, within ±50 ppb of final frequency after powered on for 1 hour

Notes:

1* All measurements guaranteed at nominal VDD, nominal load, and at +25°C unless otherwise specified.

Precision Ultra Low Phase Noise OCXO in 25x25 mm Package



ESD Sensitive

25.4 x 25.4 x 12 mm

Datasheet #456830

Electrical (cont.)


Parameters	Symbol	Condition	Min	Typ	Max	Unit	Notes
Load		AC-coupled 50 Ohm (Sine wave)					
Output Waveform		Sine wave					
Output Power			+8	+13		dBm	
Harmonics Suppression					-50	dBc	
Spurious Suppression					-80	dBc	
Control Voltage	V _c		0		4.5	V	
Linearity					10	%	
Input impedance	Z _{in}	At V _c pin	100			kOhm	
Pull range		from nominal F	±2			ppm	

Environmental and Mechanical

Parameter	Description
Operating temperature range	-40°C to +85°C standard
Vibration	Test Condition: 0.75mm ;acceleration:10g;10Hz~500Hz, one cycle per 30 min, test 2 hour. (3 times for each 3 directions X ,Y , Z), IEC 68-2-06 Test Fc.
Soldering conditions	260°C for 10s Max leads only
MSL	N/A
ESD Level	Human Body Model, class2: 2000V to 4000V; ANSI/ESDA/JEDEC JS-001-2010.
	Machine Model, class B: 200V to 400V; JEDEC JESD22-A115C.



Test Circuit



Creating a Part Number

Q - C25AC - V - XXXX - 100.000 MHz - X

OCVCXO

Supply voltage	
Code	Specification
B	5V ± 5%

Output	
Code	Specification
S	Sine wave

Temperature Stability	
Code	Specification
K	±3x10 ⁻⁸

Packaging	
Blank	Bulk

Output Frequency	
Please specify the frequency in units of MHz out to 3-digit accuracy after the decimal. Example: 100.000MHZ	

Temperature Range	
Code	Specification
M	-40°C to 85°C

Not all combinations are available. Consult Factory.

Please see the table below for developed part numbers.


Developed Part Numbers		
O-C25AC-V-BSKM-100.000MHz		

Precision Ultra Low Phase Noise OCXO in 25x25 mm Package




25.4 x 25.4 x 12 mm
Datasheet #456830


Typical Phase Noise



Typical Allan Deviation



Mechanical Dimensions



Dimensions: inches [mm]

Pin #	Function
1	Output
2	GND
3	Control Voltage
4	No Connect
5	Vcc

Precision Ultra Low Phase Noise OCXO in 25x25 mm Package



ESD Sensitive

25.4 x 25.4 x 12 mm
Datasheet #456830

Packaging

Bulk Tray