



APARM1504-SG3

Request Samples



Check Inventory



15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A



Features

- GPS/GLONASS/Galileo/Beidou Patch Antenna
- Compact Size: 15.0 x 15.0 x 4.0 mm
- Peak Gain: 1.9 dBic
- Antenna Efficiency: 70%
- RHCP Polarization
- Through Hole Mounting
- Light Weight: 5.27 g

Applications

- GNSS Modules
- UAVs and Drones
- Asset Tracking & Telematics
- Intelligent Transportation
- Precision Agriculture
- Geolocation and Tracking

Product Image





APARM1504-SG3

Request Samples



Check Inventory




15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

GNSS Frequency Bands Covered

GPS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
	■	□	□	
GLONASS	G1 1598.06-1609.31MHz	G2 1242.93-1251.68MHz	G3 1202.025MHz	
	■	□	□	
Galileo	E1 1575.42MHz	E5a 1176.45MHz	E5b 1201.5MHz	E6 1278.75MHz
	■	□	□	□
BeiDou	B1I 1561MHz	B2 1207.14MHz	B3 1268.52MHz	
	■	□	□	
QZSS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	L6 1278.75MHz
	■	□	□	□
IRNSS/NAVIC			L5 1176.45MHz	
			□	
SBAS	L1/E1/B1 1575.42MHz		L5/B2a/E5a 1176.45MHz	
	■		□	



Frequency allocation: GNSS systems, upper L bands and lower L bands



APARM1504-SG3

Request Samples



Check Inventory



15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Electrical Specification

Parameters	Typ.			Units	Note
Frequency	1561 (B1I)	1575.42 (L1/E1)	1602 (G1)	MHz	
VSWR	< 2.0			-	
Peak Gain	-0.7	0.7	1.9	dBic	
Average Gain	-4.0	-3.4	-1.7	dBic	
Maximum Efficiency	40	45	70	%	
Average Efficiency	39	43	63	%	
Polarization	RHCP			-	(Right Hand Circular Polarization)
Nominal Impedance	50			Ω	

Note: All measurements were performed using the evaluation board in a free-space environment. Actual performance may vary depending on factors such as the ground plane, specific application, and surrounding environment.

Mechanical Specification

Parameter	Specification
Antenna Dimension	15.0 x 15.0 x 4.0 mm
Evaluation Board Dimension	70 x 70 mm
Mounting Type	Through Hole & Adhesive
Mounting Location	PCB Center Mounting
Material(s)	Ceramic
Weight	5.27 g

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +105°C
Storage Temperature	-40°C to +105°C
RoHS Compliance	Yes

GPS/GLONASS/Galileo/Beidou Patch Antenna



APARM1504-SG3

Request Samples



Check Inventory



15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Ordering Information

Part Number	Description
APARM1504-SG3	GPS/GLONASS/Galileo/Beidou Patch Antenna
APARM1504-SG3-EVB	GPS/GLONASS/Galileo/Beidou Patch Antenna EVB



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-11-25




ABRACON IS
ISO9001-2015
CERTIFIED

**APARM1504-SG3**

Request Samples



Check Inventory

**15.0 x 15.0 x 4.0 mm****RoHS Compliant****MSL Level = N/A****Product Dimensions***Unit: inches[mm]*



APARM1504-SG3

Request Samples



Check Inventory




15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Measurement Setup





**APARM1504-SG3**

Request Samples



Check Inventory

**15.0 x 15.0 x 4.0 mm****RoHS Compliant****MSL Level = N/A****Reflection Characteristics – Return Loss & VSWR**



APARM1504-SG3

Request Samples



Check Inventory





15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Radiation Characteristics – Peak Gain & Average Gain





APARM1504-SG3

Request Samples




Check Inventory



15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Radiation Characteristics – Total Efficiency (%)



APARM1504-SG3

Request Samples



Check Inventory




15.0 x 15.0 x 4.0 mm

RoHS Compliant


MSL Level = N/A

Antenna Footprint & PCB Layout Guide

Top



Bottom



Unit: mm

Note: Antenna welding does not support reflow soldering, please use manual soldering, the recommended soldering time is $\leq 3s$, and the temperature is $390 \pm 20^{\circ}C$.

For technical assistance, please contact [Abracon online support](#) through our online support platform.

Transmission Line

The transmission line should be kept as short as possible and be designed to have a characteristic impedance of 50Ω. Abracon recommends using a Co-Planar Waveguide with Ground (CPWG), which dimensions can be derived by any trusted calculator, using the correct input for PCB materials and layer stack-up.



APARM1504-SG3

Request Samples



Check Inventory



15.0 x 15.0 x 4.0 mm


RoHS Compliant

MSL Level = N/A


Integration Guide




Top with Antenna



Top without Antenna



Bottom with Connector



Bottom without Connector

Unit: mm



APARM1504-SG3

Request Samples



Check Inventory





15.0 x 15.0 x 4.0 mm

RoHS Compliant


MSL Level = N/A

Radiation Characteristics – 3D & 2D Pattern


1561MHz




XY plane



XZ plane



YZ plane





APARM1504-SG3

Request Samples



Check Inventory





15.0 x 15.0 x 4.0 mm


RoHS Compliant

MSL Level = N/A


1575MHz




XY plane



XZ plane



YZ plane





APARM1504-SG3

Request Samples



Check Inventory





15.0 x 15.0 x 4.0 mm


RoHS Compliant

MSL Level = N/A


1602MHz




XY plane



XZ plane



YZ plane



GPS/GLONASS/Galileo/Beidou Patch Antenna



APARM1504-SG3

Request Samples



Check Inventory



15.0 x 15.0 x 4.0 mm

RoHS Compliant

MSL Level = N/A

Packaging

50 pcs per tray

1600 pcs per carton

The carton is of dimension 330 x 280 x 254 mm

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-11-25

ABRACON IS
ISO9001-2015
CERTIFIED