


UBBL24

Technical Datasheet



Features

- Off-the-shelf convenience
- Wire or connector terminals
- Full circuit protection
- Thermistor wire option
- Meets all UN transportation testing
- Long cycle life
- High energy density
- Wide operating temperature range
- Lightweight
- No memory effect

Applications

- Portable electronics
- Hand-held devices
- Medical equipment
- Back-up power

Accessories Optional

- UCH0037-S: Wall Wart charger (U.S.)
- UCH0037-I: Wall Wart charger (International)
- UCA0102-01: Interface cable for UBBL24-FL
- UCA0102-02: Interface cable for UBBL24-C1
- UCA0102-03: Interface cable for UBBL24-C2-TH

Technical Specifications

Part No.	UBBL24-FL or UBBL24-C1 UBBL24-FL-TH or UBBL24-C2-TH
Voltage Range	5.0 to 8.4V
Average Voltage	7.2V
Capacity	5.7Ah @ C/5 Rate @ 23°C±2°C
Max. Discharge	3.0A continuous
PTC	Rated for 3.8A Hold Current @ 20°C
Thermistor	10KΩ NTC: only for UBBL24-FL-TH and UBBL24-C2-TH
Energy	41.0Wh
Energy Density	214Wh/Kg, 534Wh/l
Weight	~191g
Cycle Life	> 300 cycles @ C/5 to 80% of initial capacity
Memory	No Memory Effect
Operating Temperature	-20°C to 60°C
Storage Temperature	-20°C to 50°C
Self-Discharge	< 10% per month
Exterior/Housing	PVC Shrink Wrap
Terminals/Connector	FL: 22 AWG wire leads Red (+), Black (-) C1: JST Connector VHR-2N C2: Molex Connector 22-01-3037
Safety	Material Safety Datasheet - MSDS041 Safety Guide UBI-5112
Transportation	UN Testing Summary - UNTS-0277 Excepted from regulations for packages with gross mass of 10kg or less (consult Ultralife)
Protection	Over Voltage Limit: 4.35±0.025V (per cell) Under Voltage Limit: 2.30±0.1V (per cell) Over Discharge Current Limit: 3.0 - 5.5A
Charging	Recommended charge rate is 932mA to 8.4V in a temperature range of 0°C to 45°C. Hold at 8.4V until current declines to 100mA. Maximum charge rate is 3.0A @ 23°C±2°C.


Dimensions

UBBL24-FL: wire leads

UBBL24-C1: connector

UBBL24-FL-TH: wire leads with thermistor

UBBL24-C2-TH: connector with thermistor



Performance Graphs

