

Product data sheet

Characteristics

8940XC4S2V02SY61

Pump Panel, NEMA Type S, Well Guard, oil field, Size 1, 27A, 10 HP, HLL36030M71 circuit breaker, melting alloy overload, 120 VAC 60 Hz coil, NEMA 3R



Main

Product	Well-Guard Control
Type	S2
Device Application	Pumping

Complementary

Control Circuit Type	Separate control circuit
Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Line Rated Current	27 A
Number of Poles	3
Horsepower Rating	10 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Disconnect Type	Associated circuit breaker
Circuit breaker CT rating	30 A
Circuit breaker type	HLL
Thermal overload type	Melting alloy
Protection Type	Overload
Device mounting	Surface
Electrical Connection	Screw terminal
NEMA size	1
Height	38.50 in (978 mm)
Width	20.43 in (519 mm)
Depth	9.41 in (239 mm)

Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

Ordering and shipping details

Category	21395 - 8940 XC,XD
Discount Schedule	CP1
GTIN	785901057123
Nbr. of units in pkg.	1
Package weight(Lbs)	89.00 lb(US) (40.37 kg)

Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	38.50 in (97.8 cm)
Package 1 width	20.43 in (51.9 cm)
Package 1 Length	9.41 in (23.9 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------