

Product data sheet

Characteristics

ACF115

APC Rack Air Removal Unit SX Fan Assembly

100-240V 50/60 Hz



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	100 V 120 V 200 V 208 V 230 V
Plug standard	IEC 60320 C14 NEMA 5-15P
Number of cables	2
Provided Equipment	Installation guide

General

Air flow	1600 ft ³ /min (755.12 l/s)
----------	--

Physical

Color	Black
Height	53.27 in (135.3 cm)
Width	22.99 in (58.4 cm)
Depth	7.52 in (19.1 cm)
Net Weight	104.21 lb(US) (47.27 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	1200 W
Input Frequency	50/60 Hz

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Conformance

Product Certifications	CUL Listed CE UL Listed VDE VCCI
Standards	EN 55022 Class A EN 55024 FCC Part 15 class A ICES-003 IEC 61000-3-2 IEC 61000-3-3

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Ambient Air Temperature for Storage	32...122 °F (0...50 °C)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)
Acoustic level	79 dBA

Communications & Management

Control panel	Multi-function LCD status and control console
---------------	---

Ordering and shipping details

GTIN	731304240983
Package weight(Lbs)	125.27 lb(US) (56.82 kg)

Packing Units

Package 1 Height	60.00 in (152.4 cm)
Package 1 width	32.01 in (81.3 cm)
Package 1 Length	12.01 in (30.5 cm)

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------