

Product data sheet

Characteristics

TSXCANCADD3

CANopen cordset - molded female SUB-D9
connectors - standard - IP20 - 3 m



Main

Range of Product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	9.84 ft (3 m)

Complementary

Electrical connection	2 female connectors SUB-D 9
Marking	CE
Net Weight	0.65 lb(US) (0.295 kg)

Environment

IP Degree of Protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531-PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	3595863860177
Returnability	No
Country of origin	PT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.500 cm)
Package 1 Width	8.27 in (21.000 cm)
Package 1 Length	10.83 in (27.500 cm)
Package 1 Weight	10.72 oz (304.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	25
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	17.67 lb(US) (8.016 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------