

Product data sheet

Characteristics

DE1DS1

TeSys LE - enclosure for DOL starter - with 2 pushbuttons



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or Component Type	Enclosure
Material	Polycarbonate
Device composition	Contactor ordered separately Thermal overload relay ordered separately
Product Compatibility	LE1D09 LE1D12
Control type	Push-button start Green I Push-button stop/reset Red O

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	6.54 in (166 mm)
Width	3.46 in (88 mm)
Depth	5.91 in (150 mm)
Product Weight	0.66 lb(US) (0.3 kg)

Environment

IP degree of protection	IP65 IEC 60529
IK degree of protection	IK07 IEC 60529
Ambient air temperature for operation	23...104 °F (-5...40 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	18401 - WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
GTIN	3389110087048
Nbr. of units in pkg.	1
Package weight(Lbs)	18.98 oz (538 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.98 in (15.2 cm)
Package 1 width	6.93 in (17.6 cm)
Package 1 Length	8.19 in (20.8 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Weight	63.05 lb(US) (28.6 kg)
Package 2 Height	28.94 in (73.5 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)
Package 3 Height	31.50 in (80 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------