

# Product data sheet

## Characteristics

# ACRH301P

InRow Dual Coil 300mm 27kW Indoor Unit,  
200-240V, Humidifier & Reheat, CE/UL



### Overview

Lead time      Usually in Stock

### Main

Main Input Voltage	AC 1 phase
Number of rack unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

### General

Humidification Value	6.6 lb/hr (2.99 kg/hr)
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	2912 ft <sup>3</sup> /min (1374.31 l/s)

### Physical

Color	Dark grey
Height	78.39 in (1991 mm)
Width	11.81 in (300 mm)
Depth	43.11 in (1095 mm)
Net Weight	440.92 lb(US) (200 kg)

### Input

Input power	930 W
Input Frequency	50-60 Hz

### Conformance

Product Certifications	CE UL RCM
------------------------	-----------------

### Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

### Ordering and shipping details

GTIN	731304422945
------	--------------

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--