

Product data sheet

Characteristics

TCSECU3M3M1S4

Ethernet ConneXium cable - shielded twisted pair - 2 x rugged RJ45 - UL - 1 m



Main

Range of Product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Product or Component Type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network
Cable length	3.28 ft (1 m)

Complementary

Transmission support medium	Twisted shielded pairs cable
Communication network category	5e
AWG Gauge	AWG 24
Electrical connection	2 connectors, RJ45 straight 8
Marking	UL
Cover Material	PVC

Environment

IP Degree of Protection	IP20
Standards	UL 444 CMG FT4 EIA/TIA-568 category CAT 5E IEC 11801 class D EN 50173 class D

Ordering and shipping details

Category	18225-PLC NTWRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	3595864142920
Returnability	No
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 in (1.000 cm)
Package 1 Width	7.68 in (19.500 cm)
Package 1 Length	11.81 in (30.000 cm)
Package 1 Weight	2.65 oz (75.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	30
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	5.73 lb(US) (2.600 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------