

Product data sheet

Specifications

SQUARE D



Mini circuit breaker, E-Frame, 30A, 1 pole, 277VAC, 65kA max, bolt on, 30mA ground fault protection [TAA]

EGB14030EPD

Product availability: Stock - Normally stocked in distribution facility

Main

Range	125 A Frame EDB-EGB-EJB
Product Type	Miniature circuit-breaker
Device Short Name	EGB
Earth-leakage Protection Class	Class B
Module Type	E-Frame
Trip Unit Rating	875 A

Complementary

Rated Current	30 A
Maximum Operating Voltage	277 V AC
AWG Gauge	AWG 14...AWG 6 6 copper AWG 12...AWG 4 aluminium
Breaking Capacity	35 kA 277 V AC 35 kA 240 V AC 65 kA 120 V AC 35 kA 120/240 V AC
Circuit Breaker Application	HACR rated HID rated
Earth-leakage Sensitivity	30 mA
Electrical Connection	Lugs aluminium
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number of Poles	1
Number of Spaces	2
Number of Spaces Required	2
Product Destination	NF panelboard
Protect Type	Short-circuit Overload
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	G
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.004...0.02 in ² (2.5...16 mm ²) (AWG 14...AWG 6)
Height	6.64 in (168.66 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	1.96 in (49.78 mm)
Depth	4.05 in (102.87 mm)
Product Weight	2 lb(US) (0.9 kg)

Environment

Product Certifications	cULus
Ambient Air Temperature for Operation	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200946
Discount Schedule	ODE2
GTIN	785901590545
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.50 in (6.350 cm)
Package 1 Width	5.30 in (13.462 cm)
Package 1 Length	7.20 in (18.288 cm)
Package weight(Lbs)	33.279 oz (943.471 g)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
SCIP Number	8781af64-acd9-485c-9a86-abcd458e3
REACH Regulation	REACH Declaration


Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
Take-back	No

Technical Illustration

Dimensions



All dimensions are approximate.
Also see technical drawings and/or documentation.