

# Product data sheet

Specifications

SQUARE D



Mini circuit breaker, E-Frame, 20A, 1 pole, 277VAC, 100kA max, bolt on, 30mA ground fault protection [TAA]

EJB14020EPD

**Product availability:** Non-Stock - Not normally stocked in distribution facility

## Main

Range	125 A Frame EDB-EGB-EJB
Product Type	Miniature circuit-breaker
Device Short Name	EJB
Earth-leakage Protection Class	Class B
Module Type	E-Frame

Trip Unit Rating 875 A

## Complementary

Rated Current	20 A
Maximum Operating Voltage	277 V AC
AWG Gauge	AWG 14...AWG 6 copper AWG 12...AWG 4 aluminium
Breaking Capacity	65 kA 240 V AC 65 kA 277 V AC 100 kA 120 V AC 65 kA 120/240 V AC
Circuit Breaker Application	HACR rated Switching Duty rated HID rated
Earth-leakage Sensitivity	30 mA
Electrical Connection	Lugs aluminium
Holding Current	270 A
Local Signalling	Trip indicator
Mounting Mode	Bolt-on
Number of Poles	1
Number of Spaces	2
Number of Spaces Required	2
Product Destination	NF panelboard
Protect Type	Overload Short-circuit
Trip Unit Technology	Thermal-magnetic
Breaking Capacity Code	J
Tightening Torque	30.09 lbf.in (3.4 N.m) 0.004...0.02 in <sup>2</sup> (2.5...16 mm <sup>2</sup> ) (AWG 14...AWG 6)
Height	6.64 in (168.66 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	1.96 in (49.78 mm)
Depth	4.05 in (102.87 mm)
Product Weight	2 lb(US) (0.9 kg)

## Environment

Product Certifications	cULus
Ambient Air Temperature for Operation	104 °F (40 °C)

## Ordering and shipping details

Category	US10DE200946
Discount Schedule	ODE2
GTIN	785901484509
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	7.30 in (18.542 cm)
Package weight(Lbs)	2.059 lb(US) (0.934 kg)

## Compliance

Compliance	TAA
------------	-----

## Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
SCIP Number	8781af64-acd9-485c-9a86-abcd458e3
REACH Regulation	<a href="#">REACH Declaration</a>


## Use Again

### Repack and remanufacture

Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No

## Technical Illustration

## Dimensions



All dimensions are approximate.  
Also see technical drawings and/or documentation.