

# Product data sheet

Specifications

SQUARE D



Circuit breaker, PowerPact L,  
250A, 3 pole, 600VAC, 14kA, lugs,  
MicroLogic 3.3, 100%

LDL36250CU31X

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range	PowerPact
Product name	PowerPact L
Device short name	L-Frame
Product or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

Line Rated Current	250 A
Number of Poles	3P
Control Type	Toggle
Breaking capacity code	D
Breaking capacity	25 kA 240 V AC 50/60 Hz UL 489 18 kA 480 V AC 50/60 Hz UL 489 14 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489
[Ue] rated operational voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] rated service breaking capacity	25 kA 220/240 V AC 50/60 Hz IEC 60947-2 18 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 14 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2
[Uiimp] rated impulse withstand voltage	8 kV IEC 60947-2
Trip unit technology	Electronic, standard, MicroLogic 3.3, LI
Continuous current rating	100 %
[Ui] rated insulation voltage	750 V IEC 60947-2
Trip unit name	MicroLogic 3.3
Protection technology	Current limiter
Suitability for isolation	Yes IEC 60947-2
Utilisation category	Category A
AWG gauge	AWG 2...600 kcmil copper AWG 2...500 kcmil aluminium
Local signalling	Ready 1 LED green) Alarm 1 LED 90 % Ir orange) Alarm LED 105 % Ir red) Switched off (OFF) 1 trip indicator green)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Mounting mode</b>	Unit mount lug
<b>Mounting Support</b>	Lug
<b>Electrical connection</b>	Lugs, line Lugs, load
<b>Terminal identifier</b>	AL400L61K3
<b>Long time pick-up adjustment range</b>	0.25...1 x In
<b>Tightening torque</b>	442.5 lbf.in (50 N.m) 0.05...0.5 in <sup>2</sup> (35...300 mm <sup>2</sup> ) (AWG 2...600 kcmil) 442.5 lbf.in (50 N.m) 0.05...0.4 in <sup>2</sup> (35...240 mm <sup>2</sup> ) (AWG 2...500 kcmil)
<b>Number of slots</b>	2 auxiliary switch OF plug-in 1 alarm switch SD plug-in 1 overcurrent trip switch SDE plug-in 1 voltage release MN or MX plug-in)
<b>Power wire stripping length</b>	1.2 in (31 mm)
<b>Color</b>	Black
<b>Height</b>	13.4 in (340 mm)
<b>Width</b>	5.5 in (140 mm)
<b>Depth</b>	4.3 in (110 mm)
<b>Net Weight</b>	13.7 lb(US) (6.2 kg)
<b>Communication interface</b>	Modbus Ethernet
<b>Circuit breaker application</b>	HACR rated

## Environment

<b>Standards</b>	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
<b>Product certifications</b>	UL CSA NOM
<b>IP degree of protection</b>	Front cover IP40
<b>Pollution degree</b>	3 IEC 60947-1
<b>Ambient air temperature for operation</b>	-13...158 °F (-25...70 °C)
<b>Ambient Air Temperature for Storage</b>	-58...185 °F (-50...85 °C)
<b>Operating altitude</b>	< 6561.68 ft (2000 m) without derating 5000 m with derating

## Ordering and shipping details

<b>Category</b>	US10DE201116
<b>Discount Schedule</b>	ODE2
<b>GTIN</b>	785901980254
<b>Returnability</b>	Yes
<b>Country of origin</b>	US

## Packing Units

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

<b>Nbr. of units in pkg.</b>	1
<b>Package 1 Height</b>	8.75 in (22.225 cm)
<b>Package 1 Width</b>	10.75 in (27.305 cm)
<b>Package 1 Length</b>	19.50 in (49.53 cm)
<b>Package weight(Lbs)</b>	15.0003 lb(US) (6.804 kg)

## **Contractual warranty**

<b>Warranty</b>	18 months
-----------------	-----------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO<sub>2</sub> eq, Total Life cycle) **815**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant with Exemptions**

[REACH Regulation](#) [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

PVC free **Yes**

## Use Again


### Repack and remanufacture

[Circularity Profile](#) [End of Life Information](#)

Take-back **No**

## Technical Illustration

## Dimensions



All dimensions are approximate.  
Also see CAD, technical drawings, and technical documentation.