

Product data sheet

Specifications



Switch disconnector, TeSys
Control, for ON/OFF, 40A, $\tilde{A}^{\sim}22.5$
fixing, for mounting for mounting on
door

VBD2

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VBD
Device Application	Preventive maintenance
Product Type	Switch disconnector

Complementary

Device Composition	Handle Switch
Mounting Support	Handle door Switch door
Mounting Method	Hole 0.9 in (22.5 mm) handle
Performance Level	High performance
Number of Poles	3P
Contact Type and Composition	3 NO
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	11 kW 690 V AC-3) 15 kW 690 V AC-23A) 11 kW 400...415 V AC-3) 15 kW 500 V AC-3) 18.5 kW 500 V AC-23A) 5.5 kW 230...240 V AC-3) 7.5 kW 230...240 V AC-23A) 15 kW 400...415 V AC-23A)
[Ie] Rated Operational Current	29 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	40 A
[Ithe] Conventional Enclosed Thermal Current	32 A
Making Capacity (I Rms)	400 A 400 V AC-21A 400 A 400 V AC-22A 400 A 400 V AC-23A
Breaking Capacity	320 A 400 V AC-21A) 320 A 400 V AC-22A) 320 A 400 V AC-23A)
Rated Conditional Short Circuit Current	10 kA 400 V 50 A aM 10 kA 400 V 50 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Icw] Rated Short Time Withstand Current	480 A 400 V 1 s
[Uiimp] Rated Impulse Withstand Voltage	8 kV
Suitability for Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Color	Black
Handle Front Plate Color	Black
Rotary Handle Padlocking	1 to 3 padlocks 0.2...0.3 in (4...8 mm)
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-1...5
IEC Terminal Connection	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.009 in ² (6 mm ²) flexible - with cable end
Tightening Torque	Power circuit 18.6 lbf.in (2.1 N.m) screw clamp terminals
Base Dimension	60 x 60 mm
Height	2.9 in (74 mm)
Width	2.4 in (60 mm)
Product Weight	0.474 lb(US) (0.215 kg)

Environment

Standards	IEC 60947-3
Product Certifications	CSA CCC GL UL UKCA
Degree of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	TC
Mechanical Robustness	Vibrations 10...150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	Main switch disconnector

Ordering and shipping details

Category	US10CP121730
Discount Schedule	OCP1
GTIN	3389110724943
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	4.72 in (12.0 cm)
Package weight(Lbs)	7.8 oz (221.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.842 lb(US) (5.825 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	31
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	63dc4fbe-3f44-4801-881b-22a3bb8008d9
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Halogen free product
PVC free	Yes

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.