

Product data sheet

Characteristics

8501KUR13V24

Plug in relay, Type KU, blade, 0.5 HP at 240 VAC, 10A resistive at 120 VAC, 11 blade, 3PDT, 3 NO, 3 NC, 240 VAC coil



Main

Product range	8501K
Product type	Relay
Relay Type	General purpose
Mounting type	Socket
Contact composition	3PDT
[Uc] control circuit voltage	240 V AC
Pilot light	No indicator

Complementary

Horsepower rating	1 Hp 277 V AC 0.33 hp 120 V AC
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 277 V AC resistive control circuit UL 508 10 A 30 V DC resistive control circuit UL 508
Maximum switching voltage	300 V AC 30 V DC
Contact material	Silver alloy (AgNi)
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR82

Environment

Ambient temperature range - operational	-40...131 °F (-40...55 °C)
Product certifications	UL Listed UL Recognized CSA CE
Height	2.25 in (57.15 mm)
Width	1.37 in (34.80 mm)
Depth	1.4 in (35.56 mm)

Ordering and shipping details

Category	21144-8501 KU
Discount Schedule	CP2
GTIN	785901338512
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	1.70 in (4.318 cm)
Package 1 Length	3.00 in (7.62 cm)
Package 1 Weight	3.20 oz (90.718 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile