


Product data sheet

Characteristics

GUPXCK50F

NEMA 12 (IP54) Filters Kit for GUTOR PXC UL 25/37.5/50 kVA UPS



Overview

Presentation	Dust filter kits to achieve NEMA type 12 (IP54) protection rating for 25- 50kVA UPS solutions
Lead time	Usually in Stock

Physical

Height	8.50 in (21.6 cm)
Width	8.50 in (21.6 cm)
Depth	0.39 in (1 cm)
Net Weight	0.99 lb(US) (0.45 kg)
Mounting Mode	Not rack-mountable

Conformance

Standards	FCC Part 15 class A UL 1778
-----------	--------------------------------

Environmental

Ambient Air Temperature for Operation	14...104 °F (-10...40 °C)
Operating altitude	0...9842 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage altitude	0...16404 ft (0.00...4999.94 m)
Storage Relative Humidity	Non-condensing 0...95 %

Ordering and shipping details

Nbr. of units in pkg.	1
Package weight(Lbs)	2.00 lb(US) (0.908 kg)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.00 in (25.4 cm)
Package 1 width	10.00 in (25.4 cm)
Package 1 Length	7.99 in (20.3 cm)

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.