



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	100...120 V 200...240 V
Number of rack unit	42U
Provided Equipment	Installation guide Integrated network management Network Management Card Optional concrete pad User Manual

General

Compressor Type	Scroll
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Refrigerant Charge	33 lb(US) (14.97 kg)
Air flow	3400 ft ³ /min (1604.62 l/s)
Piping Material	Copper

Physical

Height	78.39 in (199.1 cm)
Width	11.81 in (30 cm)
Depth	43.11 in (109.5 cm)
Net Weight	352.70 lb(US) (159.98 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
USB compatible	No

Input

Number of Power Feeds	2
Input power	850 W
Minimum Circuit Amp Capacity	20 A
Input Frequency	50/60 Hz
Maximum Overcurrent Protection	25 A

Conformance

Product Certifications	CUL Listed CE UL Listed
------------------------	-------------------------------

Environmental

Ambient Air Temperature for Operation	-13...104 °F (-25...40 °C)
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Acoustic level	77.1 dBA

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

Ordering and shipping details

GTIN	731304344773
Package weight(Lbs)	440.90 lb(US) (199.99 kg)

Packing Units

Package 1 Height	84.72 in (215.2 cm)
Package 1 width	26.02 in (66.1 cm)
Package 1 Length	44.76 in (113.7 cm)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---